

FG26C0G1H104JNT06



Application

Commercial Grade

Series

FG26

Dimensions

L 5.5mm Max.
W 6mm Max.
T 3.5mm Max.
F 5mm +0.8,-0.2mm
d 0.5mm +0.1,-0.03mm

Temperature Characteristic

-55 to 125°C 0+/-30ppm/°C

Rated Voltage

50Vdc

Capacitance

100nF

Capacitance Tolerance

+/-5%

O Factor


1000 Min.

Insulation Resistance


5000Mohm Min.

AEC-Q200


No




|Z| vs. Freq. Characteristic



DC Bias Characteristic



Cap. vs. Freq. Characteristic



Temperature Characteristics

