

Technical data sheet

Surge protection module for Modul 45 with audible signalling
Item no. 6117465



Surge protection / network fine protection, type 3, according to EN 61643-11 for installation in Rapid 45 trunking, device installation trunking and underfloor systems.

- Version-A with acoustic function display (switchable signal tone)
- Quick and easy mounting
- Low construction width of 22.5 mm
- Colour: Pure white; RAL 9010


Application: The surge protection device secures downstream and nearby sockets.



Additional product text 1
Additional product text 2

Surge protection device Type 3 (Class D) to VDE 0675 Parts 6-11 (DIN EN 61643-11)
for installation in Rapid 45 trunking, device installation trunking and underfloor systems.

Dimensions



Master data

Item no.	6117465
Type	ÜSS 45-A-RW
Description 1	Surge protective Modul 45
Description 2	with acoustic signal
Dimension	255V
Colour	Pure white

Technical data sheet

Surge protection module for Modul 45 with audible signalling


Item no. 6117465



Master data

RAL number	9010
Smallest sales unit (VG)	1,00 Piece
Weight	2,80 kg/100 pc.

Technical data



SPD to EN 61643-11	Type 3
SPD to IEC 61643-11	Class III
Test class, type 3	☒
Nominal voltage	230,00 V
Maximum continuous voltage AC	255,00 V
Max. continuous operating voltage	255,00 V
Nominal discharge current (8/20)	2.5 kA
Rated current	16,00 A
Maximum discharge current (8/20 µs)	5,00 kA
Arrestor surge current (8/20) [total]	5,00 kA
Combined voltage protection level [L-PE]	1.500,00 kV
Protection level	1,5 kV
Protection level [L-N]	1.500,00 kV
Protection level (L-N)	< 1,5 kV
Protection level (N-PE)	< 1,5 kV
Response time	25 ns
Maximum back-up fuse	16,00 A
Temperature range	-25-+45 °C
Version	Acoustic function display
Installation type	Duct installation
Protection rating	IP20
Protection rating	IP 20
Blow-out	☐
Telecommunications contact	☐
Conductor cross-section, rigid (single wire/multi-wire)	- 1,50 mm²
Connection cross-section, rigid	1,50 - 1,50 mm²
Signalling on device	Acoustic