




Pushing Performance
Since 1945



PEOPLE. POWER. PARTNERSHIP.

HARTING Selection Guide

Han-Modular® Connectors

Description of the Han-Modular® system

The Han-Modular® series is designed for combining different transmission media in one connector. The multifaceted system of inserts, contacts, frames, hoods and housings as well as accessories fulfils individual customer requirements. The customer can choose between more than 100 different modules. These are suitable for different transmission media and cover various termination techniques. The patented Han-Modular® hinged frame enables the configuration of all modules in the well-accepted Han® hoods and housings.




Further additional solutions are available, e.g. suitable docking frames for drawer units. Individual customer requirements can be realised by means of the Han-Modular® series. Combining various transmission media in one single connector results in lower expenditures in installation time and production downtime. Space savings and cost savings are further benefits. The easy extension possibilities secure the ideal solution for an actual as well as future safe design.

Highlights

- Combination of different connectors to one unit**
- Shorter installation times**
- Important space saving**
- Save money for components as well as for the whole industrial site**
- Future safe design due to easy extensions**

System description




Technical characteristics

Specifications and approvals	
- DIN EN 61984 / DIN EN 60664-1	
- UL File No. E235076 / E318390	
- DNV GL Certificate No. TAE00003MY / TAA00002EU	
PE system (hinged frame)	2 leading PE contacts
- Signal side	0.5 ... 2.5 mm²
- Power side	4 ... 10 mm²
	(10 mm² with crimp tool 09 99 000 0374)
Limiting temperatures*	- 40 °C ... + 125 °C
Flammability acc. to UL 94	V0
Working life	
- Standard version	> 500 mating cycles
- HMC version	> 10.000 mating cycles
Material	
- Hinged frames	zinc die cast
- Modules	polycarbonate
- Contacts	copper alloy
* Some modules have a lower limiting temperature (i.e. pneumatic, optical as well as data transmission modules)	

Configuration of the Han-Modular® connectors

Use the Han® Online Configurator and quickly and easily assemble your Han-Modular® interface and benefit from the advantages.

- Ensure the compatibility of the components with each other
- Selection always in view through interactive 3D visualization
- Documentation via download package for the complete interface
- Working in a team using the save, load and share function



You can find the Han® configurator at: www.harting.com/configurator

Hinged Frames Plus

Hinged Frames Plus – the market standard



Suitable for more than 100 different modules



Quick and easy assembly supported by an audible “Click”




Very high mechanical stability



No tools for insertion and removal



2 leading PE contacts



Size	Hinged frames 6 B	Hinged frames 10 B	Hinged frames 16 B	Hinged frames 24 B
Number of modules	for 2 modules	for 3 modules	for 4 modules	for 6 modules
Hinged frames (A ... F)	09 14 006 0361	09 14 010 0361	09 14 016 0361	09 14 024 0361
Hinged frames (a ... f)	09 14 006 0371	09 14 010 0371	09 14 016 0371	09 14 024 0371
HMC Hinged frames (A ... F)	09 14 206 0303	09 14 210 0303	09 14 216 0303	09 14 224 0303
HMC Hinged frames (a ... f)	09 14 206 0313	09 14 210 0313	09 14 216 0313	09 14 224 0313

Accessories


Size	Han-Modular® Guard for hinged frames plus	Coding element Han® 6 B - 24 B	Guide pins / bushes Han® 6 B - 24 B	Han® 10 A frame for 1 module
Note	Guiding, colour coding, protection	6 codings	16 codings	
Part number	09 14 000 999x	09 14 000 9901	Male: 09 14 000 9908 Female: 09 14 000 9909	09 14 000 0304

* for pneumatic, optical as well as small contacts (≤ 5 A) guide pins and bushes are recommended

Docking frame

Docking frame

- Docking connector for drawer systems
- Robust, leading guide pins and bushes
- Cost saving polycarbonate frames
- Compatible with HMC up to 10.000 mating cycles
- Large tolerance compensation of ± 2 mm play (float mount with M4 adapter plate 09 14 000 9936)
- Removal of the modules with tool 09 99 000 0331



Size	Docking frames 6 B	Docking frames 10 B	Docking frames 16 B	Docking frames 24 B
Number of modules	for 2 modules	for 3 modules	for 4 modules	for 6 modules
Dimensions	65.8 x 33 mm	79.3 x 45 mm	94 x 45 mm	123.4 x 45 mm
float mounting (A ... F)	09 14 006 1701	09 14 010 1701	09 14 016 1701	09 14 024 1701
fix mounting (a ... f)	09 14 006 1711	09 14 010 1711	09 14 016 1711	09 14 024 1711
Cover		09 14 010 5701	09 14 016 5701	09 14 024 5701

Han-Modular® Hoods/Housings



Han-Modular® Hoods/Housings		Han-Modular® Compact	Han-Modular® Twin	Han-Modular® Eco	Han-Modular® Eco
	Hoods/Housings type Number of modules PE termination	Metal hoods/housings IP65 1 module 0.5 ... 10 mm²	Metal hoods/housings IP65 2 modules 0.5 ... 10 mm²	Plastic hoods/housings IP65 1 module without PE	Plastic hoods/housings IP65 1 module Pin 1 = PE
	Hoods - Carrier hoods - Hood side entry M25 - Hood top entry M25 - Hood top entry M32 - Cover	09 14 001 0311 19 14 001 0501 19 14 001 0401 19 14 001 0402 09 14 001 5402	09 14 002 0311 19 14 002 0501 19 14 002 0401 19 14 002 0402	09 14 001 0420	09 14 001 0421
	Housings - Bulkhead-mounted housing - Cable to cable housing - Cover	09 14 001 0301 09 14 001 0301 + Hood 09 14 001 5401	09 14 002 0301 09 14 002 0301 + Hood 09 14 002 5401	09 14 001 0320 09 14 001 0720	09 14 001 0321 09 14 001 0721
	Coding elements	09 14 000 997x		09 14 000 9929	09 14 000 9929
Han-Modular® Hoods/Housings		Han-Eco® Modular	Han-Yellock®	Han-Modular® Flexbox	Module clamp
	Hoods/Housings type Locking element Field of application Number of modules	Plastic hoods/housings IP65 Plastic levers Industrial applications 3, 4, 5, 7 modules	Metal hoods/housings IP65 Press-button Industrial applications 2, 4 modules	Plastic hoods/housings IP54 screw locking e.g. energy chain up to 4 x 4 modules	Plastic mounting frame IP20 Snap locking within switch cabinet 1 module
Hoods/housings for hinged frame	Part numbers	19 41 ...	11 ...	09 14 000 8...	09 14 000 0312 09 14 000 0313
Hoods/housings for hinged frame		Han® B	Han® EMV	Han® M	Han® HPR
	Hoods/Housings type Locking element Field of application	Metal hoods/housings IP65 Han-Easy Lock® Industrial applications	Metal hoods/housings IP65 Han-Easy Lock® shielded connections	Metal hoods/housings IP65 Stainless steel levers Outdoor applications	Metal hoods/housings IP68 Screw locking Rail technology
	Sizes: - Han® 6 B for 2 modules - Han® 10 B for 3 modules - Han® 16 B for 4 modules - Han® 24 B for 6 modules - Han® L32 B for 8 modules				
Hoods/housings for hinged frame	Part numbers	09 30 ... / 19 30 ...	09 62 ... / 19 62 ...	09 37... / 19 37...	09 40 ... / 19 40 ...
Hoods/housings for hinged frame		Han® HMC	Han-Snap®	Grip panel	Docking frame
	Hoods/Housings type Locking element Field of application	Metal hoods/housings IP65 Han-Easy Lock® up to 10.000 mating cycles	Plastic adapter IP20 Snap locking within switch cabinet	Metal mounting frame IP20 Screw locking within switch cabinet	Metal frame IP20 without locking for drawer systems
	Sizes: - Han® 6 B for 2 modules - Han® 10 B for 3 modules - Han® 16 B for 4 modules - Han® 24 B for 6 modules				
Hoods/housings for hinged frame	Part numbers	09 30 2 ... / 19 30 2 ...	09 33 ...	09 00 0xx 56 ...	09 30 0xx 1704

For more details and part numbers refer to catalogue "Industrial Connectors Han®" as well as the HARTING eCatalogue


Crimp Contacts and Crimping Tools



5A - D-Sub	Cross-section / Wire gauge				Male contact (gold plated)	Female contact (gold plated)	Male contact (HMC gold plated)	Female contact (HMC gold plated)
	(mm²)	(AWG)						
	0.09 - 0.25	28 - 24			09 67 000 7576	09 67 000 7476	09 67 000 7570	09 67 000 7470
	0.13 - 0.33	26 - 22			09 67 000 5576	09 67 000 5476	09 67 000 5570	09 67 000 5470
	0.25 - 0.52	24 - 20			09 67 000 8576	09 67 000 8476	09 67 000 8570	09 67 000 8470
10A - Han D®	Cross-section / Wire gauge		Male contact (silver plated)	Female contact (silver plated)	Male contact (gold plated)	Female contact (gold plated)	Male contact (HMC gold plated)	Female contact (HMC gold plated)
	(mm²)	(AWG)						
	0.14 - 0.37	26 - 22	09 15 000 6104	09 15 000 6204	09 15 000 6124	09 15 000 6224	09 15 200 6124	09 15 200 6224
	0.5	20	09 15 000 6103	09 15 000 6203	09 15 000 6123	09 15 000 6223	09 15 200 6123	09 15 200 6223
	0.75	18	09 15 000 6105	09 15 000 6205	09 15 000 6125	09 15 000 6225	09 15 200 6125	09 15 200 6225
	1	18	09 15 000 6102	09 15 000 6202	09 15 000 6122	09 15 000 6222	09 15 200 6122	09 15 200 6222
	1.5	16	09 15 000 6101	09 15 000 6201	09 15 000 6121	09 15 000 6221	09 15 200 6121	09 15 200 6221
16A - Han E®	2.5	14	09 15 000 6106	09 15 000 6206	09 15 000 6126	09 15 000 6226	09 15 200 6126	09 15 200 6226
	0.14 - 0.37	26 - 22	09 33 000 6127	09 33 000 6227	09 33 000 6117	09 33 000 6217	09 33 200 6117	09 33 200 6217
	0.5	20	09 33 000 6121	09 33 000 6220	09 33 000 6122	09 33 000 6222	09 33 200 6122	09 33 200 6222
	0.75	18	09 33 000 6114	09 33 000 6214	09 33 000 6115	09 33 000 6215	09 33 200 6115	09 33 200 6215
	1	18	09 33 000 6105	09 33 000 6205	09 33 000 6118	09 33 000 6218	09 33 200 6118	09 33 200 6218
	1.5	16	09 33 000 6104	09 33 000 6204	09 33 000 6116	09 33 000 6216	09 33 200 6116	09 33 200 6216
40A - Han® C	2.5	14	09 33 000 6102	09 33 000 6202	09 33 000 6123	09 33 000 6223	09 33 200 6123	09 33 200 6223
	3	12	09 33 000 6106	09 33 000 6206				
	4	12	09 33 000 6107	09 33 000 6207	09 33 000 6119	09 33 000 6221	09 33 200 6119	09 33 200 6221
Crimping tools	Acc. to IEC 60352-2		09 99 000 0501	09 99 000 0021	09 99 000 0110	09 99 000 0377	09 99 000 0888	Removal tools
	 							
	D-Sub contacts		0.09 ... 0.82 mm²					09 99 000 0368
	Han D® contacts			0.14 ... 1.5 mm²	0.14 ... 1.5 mm²		0.14 ... 2.5 mm²	09 99 000 0012
	Han E® contacts			0.5 ... 2.5 mm²	0.5 ... 4.0 mm²		0.14 ... 4.0 mm²	09 99 000 0319
Han® HC					1.5 ... 4.0 mm²	4.0 ... 10.0 mm²	1.5 ... 4.0 mm²	09 99 000 0305
70 A	Cross-section / Wire gauge		Male contact (silver plated)	Male contact (IP20 Touch-Proof)	Female contact (silver plated)	Crimp dies acc. to DIN 46235	Battery hydraulic crimping tool	Hand-Hydraulic crimping tool
	(mm²)	(AWG)						
	10		09 11 000 6131	09 11 000 7100	09 11 000 6231	09 99 000 0852		
	16		09 11 000 6132	09 11 000 7101	09 11 000 6232	09 99 000 0853		
100 A	25		09 11 000 6133	09 11 000 7102	09 11 000 6233	09 99 000 0854		
	10		09 11 000 6114		09 11 000 6214	09 99 000 0852		
	16		09 11 000 6116		09 11 000 6216	09 99 000 0853		
	25		09 11 000 6125		09 11 000 6225	09 99 000 0854		
200 A	35		09 11 000 6135		09 11 000 6235	09 99 000 0855		
	25		09 11 000 6120	09 11 000 7120	09 11 000 6220	09 99 000 0854		
	35		09 11 000 6121	09 11 000 7121	09 11 000 6221	09 99 000 0855		
	50		09 11 000 6122	09 11 000 7122	09 11 000 6222	09 99 000 0856		
	70		09 11 000 6123	09 11 000 7123	09 11 000 6223	09 99 000 0857		
300 A	70			09 11 000 7535	09 11 000 6635	09 99 000 0867	09 99 000 0860 (120 kN)	09 99 000 0861 (120 kN)
	95			09 11 000 7536	09 11 000 6636	09 99 000 0868		
	120			09 11 000 7537	09 11 000 6637	09 99 000 0869		

Power and Signal Modules – Field assembly



100 - 300 A		Han® 300A PE module	Han® 200 A Axial module	Han® 200 A PE module	Han® 100 A Axial module	Han® PE module
						
		1 x PE* 300 A Axial screw termination	1 contact* 200 A / 1000 V Axial screw termination	1 x PE* 200 A Axial screw termination	2 contacts* 100 A / 1000 V Axial screw termination	1 x PE 100 A Axial screw termination
		95 ... 120 mm ²	40 ... 70 mm ²	40 ... 70 mm ²	16 ... 35 mm ²	16 ... 35 mm ²
	(M)	09 14 001 2681	09 14 001 2662	09 14 001 2667	09 14 002 2651	09 14 001 2633
	(F)	09 14 001 2781	09 14 001 2762	09 14 001 2767	09 14 002 2751	09 14 001 2733
			25 ... 40 mm ²	25 ... 40 mm ²	10 ... 25 mm ²	10 ... 25 mm ²
	(M)		09 14 001 2663	09 14 001 2668	09 14 002 2653	09 14 001 2632
	(F)		09 14 001 2763	09 14 002 2768	09 14 002 2753	09 14 001 2732
40 - 70 A		Han® 70 A Axial module	Han® 70 A Hybrid module	Han® 40A Axial module	Han® C Axial module	
						
		2 contacts 70 A / 1000 V Axial screw termination	1 + (4 x Han E) 70 A / 1000 V Axial screw termination	2 contacts 40 A / 1000 V Axial screw termination	3 contacts 40 A / 690 V Axial screw termination	
		14 ... 22 mm ²	14 ... 22 mm ²	6 ... 10 mm ²	6 ... 10 mm ²	
	(M)	09 14 002 2647	09 14 005 2647	09 14 002 2602	09 14 003 2602	
	(F)	09 14 002 2742	09 14 005 2742	09 14 002 2702	09 14 003 2702	
		6 ... 16 mm ²	6 ... 16 mm ²	2.5 ... 8 mm ²	2.5 ... 8 mm ²	
	(M)	09 14 002 2646	09 14 005 2646	09 14 002 2601	09 14 003 2601	
	(F)	09 14 002 2741	09 14 005 2741	09 14 002 2701	09 14 003 2701	
10 - 16 A		Han E® Quick Lock module	Han® EE Quick Lock module	Han® ES module	Han E® screw module	Han DD® Quick Lock Modul
						
		6 contacts 16 A / 500 V Quick Lock termination 0.5 ... 2.5 mm ²	8 contacts 16 A / 400 V Quick Lock termination 0.5 ... 2.5 mm ²	5 contacts 16 A / 400 V Cage clamp termination 0.14 ... 2.5 mm	5 contacts 16 A / 230/400 V Screw termination 0.5 ... 2.5 mm ²	12 contacts 10 A / 250 V Quick Lock termination 0.25 ... 1.5 mm ²
	(M)	09 14 006 2633	09 14 008 2633	09 14 005 2616	09 14 005 2601	09 14 012 2632
	(F)	09 14 006 2733	09 14 008 2733	09 14 005 2716	09 14 005 2701	09 14 012 2732

Pneumatic Modules




3 - 6 mm Tubes		Pneumatic module	Contacts (≤ 10 bar)			Module
						Number of contacts: 3 
		For tube diameter Ø	6 mm OD	4 mm OD	3 mm OD	Male module (M) 09 14 003 3501
		Male contact	09 14 000 6356	09 14 000 6354	09 14 000 6353	Female module (F) 09 14 003 3501
		Female without shut-off	09 14 000 6456	09 14 000 6454	09 14 000 6453	
8 + 10 mm Tubes		Pneumatic double module	Contacts (≤ 10 bar)			Module
						Number of contacts: 2* 
		For tube diameter Ø	8 mm OD	10 mm OD	10 mm ID	Male module (M) 09 14 002 3501
		Male contact	09 14 000 6358	09 14 000 6350	09 14 000 6310	Female module (F) 09 14 002 3502
		Female without shut-off	09 14 000 6458	09 14 000 6450	09 14 000 6410	
		Female with shut-off	09 14 000 6468	09 14 000 6460	09 14 000 6411	

(M) = Part numbers Male Module (F) = Part numbers Female Module * Double module, requires two places in the frame

Power and Signal Modules – Crimp termination




PE	Han® PE module (Including crimp contact for earthing)				
		1 x PE 35 mm² Crimp termination, Han® HC	1 x PE 25 mm² Crimp termination, Han® HC	1 x PE 16 mm² Crimp termination, Han® HC	1 x PE 10 mm² Crimp termination, Han® HC
	Male module (M) Female module (F)	09 14 001 3074 09 14 001 3174	09 14 001 3073 09 14 001 3173	09 14 001 3072 09 14 001 3172	09 14 001 3071 09 14 001 3171
70 - 300 A	Han® 300 A Crimp module	Han® 200 A Crimp module	Han® 100 A Crimp module	Han® 100 A Single module	Han® 70 A Crimp module
	 1 contact* 300 A / 1000 V 70 ... 120 mm² Crimp termination, Han® HC	 1 contact* 200 A / 1000 V 25 ... 70 mm² Crimp termination, Han® HC	 2 contacts* 100 A / 1000 V 10 ... 35 mm² Crimp termination, Han® HC	 1 contact 100 A / 830 V 10 ... 35 mm² Crimp termination, Han® HC	 2 contacts 70 A / 1000 V 6 ... 25 mm² Crimp termination, Han® HC
	(M) (F)	09 14 001 3004 09 14 001 3104	09 14 001 3003 09 14 001 3103	09 14 002 3051 09 14 002 3151	09 14 001 3031 09 14 001 3131
40 A	Han® 40 A Crimp module	Han® C module	Han® CC module	Han® CD module	Han® HV module 40 A
	 2 contacts 40 A / 1000 V 1.5 ... 10 mm² Crimp termination, Han® C	 3 contacts 40 A / 690 V 1.5 ... 6 mm² Crimp termination, Han® C	 4 contacts 40 A / 830 V 1.5 ... 6 mm² Crimp termination, Han® C	 3 + 4 contacts 40 A + 10 A / 830 V 0.14 ... 6 mm² Crimp, Han® C + Han D®	 2 contacts* 40 A 2900/5000 V 1.5 ... 10 mm² Crimp termination, Han® C
	(M) (F)	09 14 002 3002 09 14 002 3102	09 14 003 3001 09 14 003 3101	09 14 004 3041 09 14 004 3141	09 14 007 3001 09 14 007 3101
16 A	Han E® module	Han E® Protected module	Han® EE module	Han® EEE module	Han® HV Single module
	 6 contacts 16 A / 500 V 0.14 ... 4 mm² Crimp termination, Han E®	 6 contacts 16 A / 830 V 0.14 ... 4 mm² Crimp termination, Han E®	 8 contacts 16 A / 400 V 0.14 ... 4 mm² Crimp termination, Han E®	 20 contacts* 16 A / 500 V 0.14 ... 4 mm² Crimp termination, Han E®	 2 contacts 16 A / 2500 V 0.14 ... 4 mm² Crimp termination, Han E®
	(M) (F)	09 14 006 3001 09 14 006 3101	09 14 006 3041 09 14 006 3141	09 14 008 3001 09 14 008 3101	09 14 020 3001 09 14 020 3101
10 - 16 A	Han® Shielded Power module	Han DD® module	Han® DDD module	Han DD® double module	Han DD® Quad module
	 4 + 2 + shielding 16 A + 10 A / 400 V 0.14 ... 4 mm² Crimp, Han E® + Han D®	 12 contacts 10 A / 250 V 0.14 ... 2.5 mm² Crimp termination, Han D®	 17 contacts 10 A / 150 V 0.14 ... 2.5 mm² Crimp termination, Han D®	 36 contacts* 10 A / 400 V 0.14 ... 2.5 mm² Crimp termination, Han D®	 42 contacts* 10 A / 150 V 0.14 ... 2.5 mm² Crimp termination, Han D®
	(M) (F)	09 14 006 3021 09 14 006 3121	09 14 012 3002 09 14 012 3102	09 14 017 3001 09 14 017 3101	09 14 036 3002 09 14 036 3102
≤ 10 A	Han® High Density module	Han® Full High Density module	Han® Dummy module	Han® Guiding Dummy module	Han® Guiding Relay module
	 25 contacts 4 A / 50 V 0.08 ... 0.52 mm² Crimp termination, D-Sub	 36 contacts 4 A / 32 V 0.14 ... 0.52 mm² Crimp termination, D-Sub	 To fill-up empty module places	 To fill-up empty module places, additional guiding function	 2 contacts with relay function (last mate - first break) Crimp termination, Han E® Relay contacts necessary
	(M) (F)	09 14 025 3001 09 14 025 3101	09 14 036 3001 09 14 036 3101	09 14 000 9950	09 14 003 3050 09 14 003 3150

(M) = Part numbers Male Module (F) = Part numbers Female Module * Double module, requires two places in the frame

Data Transfer Modules




Han® RJ45 Modules	Han® RJ45 module		for patch cable	for IDC	for patch cable	for IDC and preLink
	- 8 contacts - cat. 6A - 10 Gbit/s					
	Part numbers		Male module (M) 09 14 001 4623	Male module (M) 09 14 001 4623	Female module (F) 09 14 001 4721	Female module (F) 09 14 001 4722
			Adapter for patch cable: 09 14 000 9966	RJ Industrial IDC: 09 45 400 1560		RJ45 female IDC: 09 14 545 1561
			Patch cable cat. 6: 09 47 474 71xx			RJ45 female preLink: 09 14 008 4720
Han® M12 Modules		Han® M12 module	Han® M12 GND module	Han® M12 inserts (cable Ø 5.5 ... 8.7 mm)		
				M12 insert X-Coded	M12 insert D-Coded	M12 insert A-Coded
		Module for two Han® M12 inserts	Version with additional shielding termination to the hinged frame	 10 Gbit/s (cat. 6A) 8 contacts + shielding 0.5 A / 32 V 0.09 ... 0.25 mm² Crimp termination, har-speed	 100 Mbit/s (cat. 5e) 4 contacts + shielding 4 A / 32 V 0.09 ... 0.52 mm² Crimp termination, D-Sub	 8 contacts + shielding 2 A / 30 V 0.13 ... 0.33 mm² Crimp termination, M12
	(M)	09 14 002 3061	09 14 002 3062	09 14 881 1805	09 14 881 1405	09 14 821 1805
	(F)	09 14 002 3160	09 14 002 3162	09 14 881 2805	09 14 881 2405	09 14 821 2805
Han-Quintax® modules		Han-Quintax® module	Han-Quintax® inserts (cable Ø 3 ... 9.5 mm)			
			Han-Quintax® insert	Han® High Density Quintax	Han® D Coax insert	Han® E Coax insert
		Module for two Han-Quintax® inserts	 100 Mbit/s (cat. 5e) 4 contacts + shielding 10 A / 50 V 0.14 ... 2.5 mm² Crimp termination, Han® D	 100 Mbit/s (cat. 5e) 8 contacts + shielding 5 A / 50 V 0.09 ... 0.52 mm² Crimp termination, D-Sub	 ≤ 500 Mhz / 75 Ω 1 contact + shielding 10 A / 50 V 0.14 ... 2.5 mm² Crimp termination, Han® D	 ≤ 500 Mhz / 50 Ω 1 contact + shielding 16 A / 50 V 0.14 ... 4 mm² Crimp termination, Han® E
	(M)	09 14 002 3004	09 15 004 3013	09 15 008 3013	09 15 001 3013	09 15 001 3023
	(F)	09 14 002 3104	09 15 004 3113	09 15 008 3113	09 15 001 3113	09 15 001 3123
	Optional shield connection to the hinged frame with the Han-Quintax metal adapter 09 14 000 9915					
Han® Gigabit & Han® Megabit Modules		Adapter module	Han® Gigabit / Han® Megabit inserts (cable Ø ≤ 14 mm)			
			Han® Gigabit insert	Han® Gigabit cat. 8 insert	Han® Megabit insert	Han® Megabit insert
		Module for one - Han Gigabit insert - Han Megabit insert - Han Shielded insert	 10 Gbit/s (cat. 6A) 8 contacts + shielding 5 A / 60 V DC 0.09 ... 0.52 mm² Crimp termination, D-Sub	 40 Gbit/s (cat. 8.2) 8 contacts + shielding 5 A / 60 V DC 0.09 ... 0.52 mm² Crimp termination, D-Sub	 2 cable entries Ø 10 mm 2 x 100 Mbit/s (cat. 5e) 2 x 4 contacts + shielding 10 A / 50 V 0.14 ... 2.5 mm² Crimp termination, Han® D	 1 cable entry 1 Gbit/s (cat. 5e) 2 x 4 contacts + shielding 10 A / 50 V 0.14 ... 2.5 mm² Crimp termination, Han® D
	(M)	09 14 001 3011	09 14 008 3011	09 14 008 3034	09 14 008 3016	09 14 008 3021
	(F)	09 14 001 3111	09 14 008 3111	09 14 008 3134	09 14 008 3116	09 14 008 3121
Shielded Modules						
						
		20 contacts + shielding 4 A / 32 V 0.09 ... 0.52 mm² Crimp termination, D-Sub	27 contacts + shielding 4 A / 32 V 0.09 ... 0.52 mm² Crimp termination, D-Sub	9 contacts + shielding 5 A / 50 V 0.09 ... 0.52 mm² Crimp termination, D-Sub	8 contacts + shielding 1 A / 50 V (USB 3.0) for USB Patchkabel	
	(M)	09 14 020 3013	09 14 027 3022	09 14 009 3001	09 14 001 4601	
	(F)	09 14 020 3113	09 14 027 3122	09 14 009 3101	09 14 001 4703	

(M) = Part numbers Male Module (F) = Part numbers Female Module * Double module, requires two places in the frame

Han-Modular® Domino Module



Just as dominoes have two separate squares, a domino module is made up of two building blocks or cubes. The cubes can be flexibly joined to form modules as required. A Han-Modular® Domino module therefore enables the transmission of power, signals, data or compressed air, as male and female contacts can be combined in one domino module. **Each domino module consists of a cube with a small tab and a cube with a large tab.**



Han® Domino Module			Han® EE Cube	Han® DD Cube	Han® HD Cube	Pneumatic Cube
			 4 contacts 16 A / 400 V 0.14 ... 4 mm² Crimp termination, Han® E	 6 contacts 10 A / 250 V 0.14 ... 2.5 mm² Crimp termination, Han® D	 16 contacts 4 A / 32 V 0.09 ... 0.52 mm² Crimp termination, D-Sub	 1 contact ≤ 10 bar 3 + 4 + 6 mm
	Male-Cube	small tab	09 14 904 1001	09 14 906 1001	09 14 916 1001	09 14 931 1001
	Female-Cube	small tab	09 14 904 1101	09 14 906 1101	09 14 916 1101	09 14 931 1001
	Male-Cube	large tab	09 14 904 2001	09 14 906 2001	09 14 916 2001	09 14 931 2001
	Female-Cube	large tab	09 14 904 2101	09 14 906 2101	09 14 916 2101	09 14 931 2001
Han® Domino Module			Han® M12 Cube	Han® M12 GND Cube	Dummy Cube	
			 for 1 Han® M12 insert (see data transfer modules)	 for 1 Han® M12 insert (with shield connection to the hinged frame)	 Place holder for extensions	
	Male-Cube	small tab	09 14 921 1001	09 14 921 1002	09 14 900 1000	
	Female-Cube	small tab	09 14 921 1101	09 14 921 1102	09 14 900 1000	
	Male-Cube	large tab	09 14 921 2001	09 14 921 2002	09 14 900 2000	
	Female-Cube	large tab	09 14 921 2101	09 14 921 2102	09 14 900 2000	

Further Modules



Coaxial & Optical Modules	Han® LC module		Han® SC module	Han® Multi module (D-Sub)	Han® Multi module (DIN)	Han® Multi double module*
	 6 FO contacts (LC) single-mode multi-mode		 4 FO contacts (SC) 1 mm POF single-mode multi-mode	 4 Coax contacts 50 + 75 Ω (RG58, RG179, RG187, RG174, RG188, RG316)	 4 Coax / FO contacts Coaxial 50 + 75 Ω 1 mm POF multi-mode	 12 Coax / FO contacts Coaxial 50 + 75 Ω 1 mm POF multi-mode
	(M)	09 14 006 4701	09 14 004 4701	09 14 004 4501	09 14 004 4501	09 14 012 4501
	(F)	09 14 006 4711	09 14 004 4711	09 14 004 4513	09 14 004 4512	09 14 012 4512
Spezielle Module & Han-Smart®	Han-Eco® PE module		ID CAN module	ID Profinet module	Surge protection module	Ethernet-switch module*
	 PE contact, for Han-Eco® hoods/housings only 1.5 ... 16 mm² Screw termination		 10 MB Flash Module for identifying industrial components CANopen communication	 32 KB Flash Module for identifying industrial components Profinet communication	 0.5 A / 24 V DC Surge protection for four single lines	 4 Ports (RJ45) Full Gigabit Ethernet
	(M)	19 41 001 2600	09 80 015 0100	09 80 615 0100	09 80 000 0101	
	(F)	19 41 001 2700	09 80 115 0200	09 80 615 0200	09 80 003 0201	09 80 113 0400

(M) = Part numbers Male Module (F) = Part numbers Female Module * Double Module, requires two places in the frame



Pushing Performance
Since 1945

HARTING.com –
the gateway to your local website.
