


Impact Wrench

33421


- Nickel chrome molybdenum square driver
- Variable speed trigger
- Muffled on front exhaust



33421

KT NO.	Square drive inch mm	Type Std/Long anvil	Std. bolt size inch mm	Free speed R.P.M	Max. torque ft.lb Nm	Overall length inch mm	Air inlet inch	Air hose ID	Air pressure bar PSI	Avg. air consumption L/min CFM	Sound DBA	Vib M/S ²	Net weight kgs lbs	
33421-040	1/2" 12.70	Std.anvil	5/8" M16	8000	500 678	6-3/4" 171	1/4" BSPT	3/8"	6.2 90	113 4.0	101.02	8.70	2.56 5.64	1 / 8
33421-041	1/2" 12.70	Std.anvil	5/8" M16	8000	500 678	6-3/4" 171	1/4" NPT	3/8"	6.2 90	113 4.0	101.02	8.70	2.56 5.64	1 / 8

33411-040 / 33412-040



33411-040



33412-040

33411-050 / 33412-050



33411-050



33412-050

KT NO.	Square drive inch mm	Type Std/Long anvil	Std. bolt size inch mm	Free speed R.P.M	Max. torque ft.lb Nm	Overall length inch mm	Air inlet inch	Air hose ID	Air pressure bar PSI	Avg. air consumption L/min CFM	Sound DBA	Vib M/S ²	Net weight kgs lbs	
33411-040	1/2" 12.70	Std. anvil	5/8" M16	8000	500 678	7-23/64" 187	1/4" BSPT	3/8"	6.2 90	113 4.0	95.22	4.85	2.60 5.73	1 / 8
33411-041	1/2" 12.70	Std. anvil	5/8" M16	8000	500 678	7-23/64" 187	1/4" NPT	3/8"	6.2 90	113 4.0	95.22	4.85	2.60 5.73	1 / 8
33412-040	1/2" 12.70	Long anvil	5/8" M16	8000	500 678	9-23/64" 238	1/4" BSPT	3/8"	6.2 90	113 4.0	95.78	4.80	2.80 6.17	1 / 8
33412-041	1/2" 12.70	Long anvil	5/8" M16	8000	500 678	9-23/64" 238	1/4" NPT	3/8"	6.2 90	113 4.0	95.78	4.80	2.80 6.17	1 / 8
33411-050	1/2" 12.70	Std. anvil	3/4" M19	8000	650 881	7-41/64" 194	1/4" BSPT	3/8"	6.2 90	125 4.4	96.50	8.13	2.80 6.17	1 / 8
33411-051	1/2" 12.70	Std. anvil	3/4" M19	8000	650 881	7-41/64" 194	1/4" NPT	3/8"	6.2 90	125 4.4	96.50	8.13	2.80 6.17	1 / 8
33412-050	1/2" 12.70	Long anvil	3/4" M19	8000	650 881	9-23/64" 238	1/4" BSPT	3/8"	6.2 90	125 4.4	96.19	6.84	3.20 7.05	1 / 8
33412-051	1/2" 12.70	Long anvil	3/4" M19	8000	650 881	9-23/64" 238	1/4" NPT	3/8"	6.2 90	125 4.4	96.19	6.84	3.20 7.05	1 / 8