



841N

Construction machinery set

129 tools



Code		 kg
97841418		35.8
	10/9	6 x 7; 8 x 9; 10 x 11; 12 x 13; 14 x 15; 16 x 17; 18 x 19; 20 x 22; 21 x 24 mm
	14	6; 7; 8; 9; 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 20; 21; 22; 24; 27; 30; 32; 34; 36 mm
	40/13/6	1/4"  No 40 3.5; 4; 4.5; 5; 5.5; 6; 7; 8; 9; 10; 11; 12; 13 mm; No 400; 404; 405/2; 405/6; 407; 415
	50/16/6	1/2"  No 50: 10; 11; 12; 13; 14; 15; 16; 17; 18; 19; 21; 22; 24; 27; 30; 32 mm No 506; 509/5; 509/10; 506; 510; 512
	504/15	1/2"  397 mm
	514	3/4"  1/2" 
	55/9/6N	3/4"  No 55: 32; 34; 36; 38; 41; 46; 50; 55; 60 mm No 552; 554; 556; 558; 559/8; 559/16
	568	1/2"  3/4" 
	102-5/6T	No 104/120 x 2; 120 x 4 mm No 105/120 x 10 mm No 106/125 mm; 150 mm No 107/125 mm
	4840	PZ1; PZ2
	4891	⊖ 4820: 0.6 x 3.5 x 75 mm 0.8 x 4.0 x 100 mm 1.0 x 5.5 x 125 mm 1.2 x 6.5 x 150 mm ⊕ 4830: PH1; PH2
	10760CV/9	1.5; 2; 2.5; 3; 4; 5; 6; 8; 10 mm
	65015180	180 mm
	65315170	170 mm
	65632250	250 mm
	65672280	280 mm
	65726240	240 mm
	66005160	160 mm
	10956	∅ 35 mm
	10961	300; 500 g
	11095/20	20 blades 0.05-1 mm
	12050	300 mm
	12050R	10 blades
	12374	
	12600	1800 g
	12935/3	3 m

Tool sets for aerospace industry

13200a

Basic tool set for aircraft mechanics (piston engine)

178 tools

Code		 kg
97846011		15.1
	12a/13	5/32; 3/16; 13/64; 7/32; 15/64; 1/4; 9/32; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16"
	13a	3/16; 13/64; 7/32; 15/64; 1/4; 9/32; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16; 19/32; 5/8; 11/16; 3/4; 25/32; 13/16; 7/8; 15/16; 1"
	230a	1/4 x 5/16; 5/16 x 11/32; 3/8 x 7/16; 7/16 x 1/2; 1/2 x 9/16; 9/16 x 5/8; 11/16 x 3/4; 13/16 x 7/8; 15/16 x 1"
	4025	size 4
	40aD/30/7QR	1/4"  No 40a: 1/8" No 40aD: 5/32; 3/16; 7/32; 1/4; 9/32; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16" No 40aDL: 5/32; 3/16; 7/32; 1/4; 9/32; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16" No 402a: 1/4; 9/32; 5/16; 11/32; 3/8; 7/16; 1/2" No 400QR; 405/2QR (2x); 405/6QR; 407QR; 412; 415 SG-QR
	409	3/8"  1/4" 
	415SGB N	1/4" 
	46a	3/8"  7/16; 1/2; 9/16; 5/8"
	427/18	3/8"   455 mm
	431	1/4"  3/8" 
	45a/22/8QR	3/8"  No 45a: 1/4; 5/16; 11/32; 3/8; 7/16; 1/2; 9/16; 5/8; 11/16; 3/4; 13/16; 7/8; 15/16; 1" No 47a: 5/16; 3/8; 7/16; 1/2; 9/16; 5/8; 11/16; 3/4" No 427/10QR; 427/6QR; 427/3QR; 428QR; 435SG-QR; 442; 443; 453QR
	1220	PH0
	1221	PH1
	1222	PH2
	1223	PH3
	13010	sizes 0; 1; 2; 3; 4; 5; 6; 8; 10
	4006/1	1/4" 
	12503	1/4" 
	4622	size 1 (1.0 x 5.5 x 100 mm) size 3 (1.2 x 8.0 x 150 mm) size 4 (1.6 x 10.0 x 175 mm)
	4632	PH1; PH2; PH3
	10760aCV/13	0.028; 0.035; 0.050; 1/16; 5/64; 3/32; 7/64; 1/8; 9/64; 5/32; 3/16; 7/32; 1/4"
	65015180	180 mm
	65105190	190 mm
	65315170	170 mm
	65516240	240 mm
	65751280	280 mm
	66005180	180 mm
	105-8/6 K	No 105/120 x 10 mm; No 108/150 x 2.5; 150 x 3; 150 x 4; 150 x 5; 150 x 6 mm
	10670	215 mm
	10955	∅ 27 mm
	10961	300 g
	12320	
	12321	

Continuation see next page