

Special automotive tools

11005 Pry bar

- head and point polished



Code	L mm	∅ mm	△ g	g	box
72090000	400	14	477	6	

11006 Lever bar

- special steel
- bright nickel-plated



Code	L mm	b mm	△ g	g	box
72090002	400	14	498	6	

11007 Lever bar

- special steel
- bright nickel-plated



Code	L mm	b mm	△ g	g	box
72090003	400	17	641	6	

10923 Body file holder

- from beech wood
- for flat blades



Code	L mm	△ g	g	box
72200002	530	302	1	

10906-10916 Spare blades for No 10905 and No 10923



Code	No	shape	teeth per inch	L mm	△ g	g	box
79060001	10906	fine, radial cut	15	350	321	10	
79060002	10907	medium, radial cut	12	350	286	10	
79060003	10908	coarse, radial cut	9	350	279	10	
79060012	10915	medium, angled cut	12	350	282	10	
79060013	10916	coarse, angled cut	9	350	252	10	

10922 Body file holder

- from beech wood
- for half round radius file blades



Code	L mm	△ g	g	box
72200001	530	255	1	

10921 File blade for No 10922

- coarse
- without swarf breaker
- half round
- radial cut



Code	teeth per inch	L mm	△ g	g	box
79060004	9	350	216	5	

12752 Tin snips

- lever action
- spring-assisted for self-opening action
- heavy duty cutting: sheet steel up to 1.8 mm or stainless steel sheet up to 1.2 mm



Code	shape	L mm	L "	△ g	g	box
75230001	L	260	10 1/2	532	1	
75230002	R	260	10 1/2	595	1	

L = left hand cutting
R = right hand cutting

12753 Tin snips

- lever action
- spring-assisted for self-opening action
- heavy duty cutting: sheet steel sheet up to 1.8 mm or stainless steel sheet up to 1.2 mm



Code	shape	L mm	L "	△ g	g	box
75240001	L	260	10 1/2	473	1	
75240002	R	260	10 1/2	473	1	

L = left hand cutting
R = right hand cutting

12727 Spot weld milling cutter

- HSSE steel
- for spot-weld removal on car body or sheet metal construction
- replaceable milling cutter size ∅ 10 mm
- cutting depth adjustment by set screw
- avoids distortion damage to sheet metal



Code	L mm	△ g	g	box
72260001	72	19	5	

12728 Replacement milling cutter



Code	L mm	△ g	g	box
79260001	13	4	10	

12729/12730 Spot weld drills

- for clean, burr-free removal of spot-weld
- self-cutting centre point avoids running off spot weld
- can be reground



Code	No	∅ mm	△ g	g	box
72270007	12729	7	18	5	
72270008	12730	8	30	5	