

6622 VDE VDE wire stripping pliers

- with adjustment screw to cut insulation only on wire or cable
- max. 5 mm Ø 10 mm² conductor cross-section



6622 7160



6622 8160

Code	L mm	Head	Handles	g
6622 7160	160	chrome plated	dip-coated insulation DIN EN 60900, AC/1000 V	180
6622 8160	160	chrome plated	insulated, with plastic sleeves, DIN EN 60900, AC/1000 V	168

6623 VDE VDE wire stripping pliers

- for wires from 0.5 to 5 mm Ø
- self adjusting
- cutter hole for cutting wire or stranded wires up to 5 mm Ø
- special steel



6623 7160



6623 8160

Code	L mm	Head	Handles	g
6623 7160	160	chrome plated	dip-coated insulation DIN EN 60900, AC/1000 V	214
6623 8160	160	chrome plated	insulated, with plastic sleeves, DIN EN 60900, AC/1000 V	184

6923 Replacement stripping knives (1 pair) for No 6623

Code	g
69230001	11

6630 VDE VDE cable shear

- for copper and light alloy cables
- easy, single handed operation
- special cutter geometry to avoid pressure marks and frayed ends
- adjustable joint
- anti-squeeze protection
- not suitable for steel or armoured cables



Code	L mm	Head	Handles	⑦	⑧	⑨	g
6630 7220	220	chrome plated	dip-coated insulation, DIN EN 60900 AC/1000 V	16	35	70	380

⑦ cutting capacity in mm² for single wire Al-/Cu-Cable
⑧ cutting capacity in mm² for multiple wire Al-/Cu-Cable

⑨ cutting capacity in mm² for thin wire Al-/Cu-Cable

