

Tube tools, other tools

12000 Universal thread restorers

- suitable for inside and outside threads



Code	size	L mm	Δ g	
72100004	ISO	230	115	10
72100003	SAE	230	118	10
72100002	WW	230	122	10

Pitch mm	metr. thread	threads per inch	Whitworth thread	SAE/US threads per inch
0,80	5	24	3/16 + 7/32	24
1,00	6 + 7	20	1/4	20
1,25	8 + 9	18	5/16	18
1,50	10 + 11	16	3/8	16
1,75	12	14	7/16	14
2,00	14 + 16	12	1/2 + 9/16	13
2,50	18, 20, 22	11	5/8 + 11/16	12
3,00	24 + 27	10	3/4 + 13/16	11

TCS 12025-13110/11



TCS



- 530 x 350 x 35 mm
- 11 pieces

Code	Δ g
96838759	2410

No	
12025	210 mm
12030	260 mm
12035	210 mm
12036	260 mm
12050	300 mm
12320	
12321	
12718	
12935/3	3 m
12965N	
13110	300 mm

900 Screw EXTRACTOR

- for left-hand threads



Code	size	for bolts	mm	"	L mm	recomm. Drill	Δ g	
71010001	1	M3-M4 1/8-5/32"	3	1/8	49	2 mm 5/64"	3	10
71010002	2	M5-M7 3/16-1/4"	3.4	9/64	54	3 mm 7/64"	6	10
71010003	3	M8 5/16"	4.9	3/16	59	5 mm 3/16"	12	10
71010004	4	M10-M12 3/8-7/16"	7	9/32	65	6.4 mm 1/4"	25	5
71010005	5	M14-M16 1/2-9/16"	9	23/64	88	8 mm 5/16"	50	5
71010006	6	M18-M22 5/8-3/4"	12	31/64	95	12 mm 15/32"	103	5

900/6T Screw EXTRACTOR set

- for left-hand threads
- in textile bag



Code	Content	Δ g	
96710101	1 each No 900 size 1-6	230	1

901 Screw EXTRACTOR

- with centre punch tip
- double-edged



Code	size	for bolts	mm	"	L mm	recomm. Drill	Δ g	
71050001	1	M5-M6 3/16-1/4"	6.35	1/4	60	3.2 mm 1/8"	6	1
71050002	2	M8-M10 5/16-3/8"	9.5	3/8	67	4.8 mm 3/16"	16	1
71050003	3	M10-M12 7/16-1/2"	12.7	1/2	75	6.4 mm 1/4"	30	1
71050004	4	M12-M16 1/2-9/16"	15.9	5/8	90	9.5 mm 3/8"	60	1
71050005	5	M16-M20 5/8-3/4"	19	3/4	90	11.1 mm 7/16"	100	1

901/5T Set of screw extractors

- for extracting sheared screws, bolts and stud screws from threaded holes
- suitable for right-hand and left-hand threads
- in textile bag



Code	Δ g	
96710505	248	1