

4820 3K DRALL® screwdrivers for slotted screws

- DIN 5265, ISO 2380
- Chrome Alloy Steel, matt chrome plated
- black tips



Code	a mm	b mm	L ₁ mm	L ₂ mm	g	
48 20 1035	0.6	3.5	75	170	63	10
48 20 1040	0.8	4.0	100	195	32	10
48 20 2055	1.0	5.5	125	220	58	10
48 20 1065	1.2	6.5	150	265	100	10
48 20 1080	1.6	8.0	175	290	120	10
48 20 1100	1.6	10.0	200	315	158	5
48 20 2100	2.0	12.0	250	375	218	5

4830 3K DRALL® cross-head screwdrivers

- Phillips-Recess®
- DIN 5262, ISO 8764
- Chrome Alloy Steel, matt chrome plated
- black tips



Code	PH size	L ₁ mm	L ₂ mm	g	
48 30 1000	0	60	155	28	10
48 30 1001	1	80	175	50	10
48 30 1002	2	100	215	70	10
48 30 1003	3	150	275	126	5
48 30 1004	4	200	325	251	5

4840 3K DRALL® cross-head screwdrivers

- POZIDRIV/SUPADRIV®
- DIN 5262, ISO 8764
- Chrome Alloy Steel, matt chrome plated
- black tips



Code	PZ size	L ₁ mm	L ₂ mm	g	
48 40 1001	1	80	175	33	10
48 40 1002	2	100	215	70	10

4856 3K DRALL® TORX® screwdrivers

- with hollow point (TORX® TAMPER RESISTANT)
- Chrome Alloy Steel, matt chrome plated
- black tips



Code	size	mm	L ₁ mm	L ₂ mm	g	
48 56 0006	T6 *	1.6	50	145	45	5
48 56 0007	T7	2.0	50	145	37	5
48 56 0008	T8	2.3	60	155	39	5
48 56 0009	T9	2.5	60	155	50	5
48 56 0010	T10	2.7	80	175	26	5
48 56 0015	T15	3.3	80	175	52	5
48 56 0020	T20	3.8	100	215	32	5
48 56 0025	T25	4.4	100	215	55	5
48 56 0027	T27	5.0	115	230	58	5
48 56 0030	T30	5.5	115	230	63	5
48 56 0040	T40	6.6	115	240	86	5

* without hollow point

4891 3K DRALL® set of screwdrivers

Set of 6 3K DRALL® screwdrivers
Content:

- ⊖ 4820: 0.6 x 3.5 x 75 mm
- 0.8 x 4.0 x 100 mm
- 1.0 x 5.5 x 125 mm
- 1.2 x 6.5 x 150 mm

⊕ 4830: PH1; PH2



Code	g	
96 48 91 10	530	1

4892 3K DRALL® set of screwdrivers

Set of 8 3K DRALL® screwdrivers
Content:

- ⊖ 4820: 0.6 x 3.5 x 75 mm
- 0.8 x 4.0 x 100 mm
- 1.0 x 5.5 x 125 mm
- 1.2 x 6.5 x 150 mm
- 1.6 x 8.0 x 175 mm

⊕ 4830: PH1; PH2; PH3



Code	g	
96 48 92 10	745	1

4899 3K DRALL® set of TORX® screwdrivers

Set of 9 3K DRALL® screwdrivers
for TORX® screws
(TORX® TAMPER RESISTANT).

Content:
⊖ 4856: T8; T9; T10; T15; T20;
T25; T27; T30; T40
(with hollow point)



Code	g	
96 48 99 10	513	1

TCS 4820/4830



- 175 x 350 x 35 mm
- 7 pieces



Code	g
96 83 81 84	555

No	Content
4820	size 0.6 x 3.5 x 75 mm size 0.8 x 4.0 x 100 mm size 1.0 x 5.5 x 125 mm size 1.2 x 6.5 x 150 mm
4830	PH1; PH2; PH3