

Product data sheet

610 088 3

Ferrule crimping tool PEW 8.88

Front insertion

- Easiest to work with when working conditions are cramped
- Huge range of applications supported in one tool (model PEW 8.88)
- Square crimp profile with 4 profiled crimp surfaces
- Self-adjusting adaptation to the required size of wire-end ferrule
- Force magnified by lever action to ensure fatigue-free working
- Specially hardened spring steel



General

Item number	610 088 3
EAN	4049002022814
Weight	520 g
Dimension	190 mm
Dimension packaging	250 x 108 x 43 mm

Specifications

Finish	black-oxide finish
Grips	2-component grips
Range of applications	Ferrules
Capacity	0.08 – 16.0 mm ² / AWG 28 – 6
Twin wire-end ferrules	2x 0.25 – 6.0 mm ² / 2x AWG 22 – 8

Classification

eCl@ss 10.1	ACD215012
ETIM 7.0	EC000168
proficl@ss 7.0	AAA946c003

With reservations regarding technical modifications and errors. Illustration may vary.