










P.C. MOUNTING

| ▲ SWITCH FUNCTION |        |               |
|-------------------|--------|---------------|
| POS. 1            | POS. 2 | POS. 3        |
|                   |        |               |
| ON                | N/A    | ON            |
| 2-3, 5-6, 8-9     | N/A    | 2-1, 5-4, 8-7 |



## NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. PLATING MATERIAL: SILVER
5. RATING: 5 AMPS @ 120VAC or 28VDC  
2 AMPS @ 250VAC
6. ELECTRIC LIFE: 40,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
7. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN.
8. DIELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL.
9. OPERATING TEMP.: -30°C to 85°C
10. ▲ DENOTES CRITICAL PARAMETER.

E-SWITCH  
MARKING ON  
OPPOSITE SIDE

|     |        |                               |         |    |
|-----|--------|-------------------------------|---------|----|
| D   | 24501  | update print                  | 9/22/20 | MW |
| C   | 15137  | CHANGE DIM. FROM 8.89 TO 8.40 | 8/5/05  | PV |
| B   | 14720  | REVISED AND REDRAWN           | 2/24/05 | AR |
| REV | PCR NO | DESCRIPTION                   | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE 1003P1T1B1VS2QE

SCALE  
2:1DATE  
6/8/2000DR  
GLGDWG  
T131023REV  
D