




RECOMMENDED PANEL CUTOUT
Panel Thickness 1.80-2.20mm



▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
ON	(ON)	ON
1-3, 4-2	1-5, 6-2	1-5, 6-2

(ON) = MOMENTARY



NOTES:

- ALL DIMENSIONS IN MM
- GENERAL TOLERANCE: X.X = ±0.4
X.XX = ±0.25
- TERM. NOS. FOR REFERENCE ONLY
- ELECTRICAL LIFE: 6,000 CYCLES
- OPERATING TEMP: 0°C to 85°C
- CONTACT RESISTANCE: 10mΩ MAX. INITIAL
- RATING: 16A 125VAC [cURus]
12A 250VAC [cURus]
1HP 125/250VAC [cURus]
- MATERIALS:
-BODY AND ACTUATOR: POLYAMIDE 6/6 (PA66)
-TERMINALS: SILVER PLATED BRASS (H62)
- ▲ DENOTES CRITICAL PARAMETER

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100796	print update	03/09/22	MW	PP2-1U7-2B2				000001010
					SCALE	DATE	DR	DWG	REV
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					1:1	8/5/2010	CAB	34-PP21U72B2	B