



## RECOMMENDED PANEL MOUNTING

| PANEL THICKNESS | $\bar{X} \pm 0.05$ |
|-----------------|--------------------|
| 0.75-1.25       | 29.65              |
| 1.25-2.00       | 30.15              |
| 2.00-3.00       | 30.50              |





| SWITCH FUNCTION                                                                   |                                                                                   |
|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
| POS. 1                                                                            | POS. 3                                                                            |
|  |  |
| (ON)                                                                              | OFF                                                                               |
| 1-1a                                                                              | OPEN                                                                              |

(ON)=MOMENTARY

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE:  $X.X \pm 0.4$   
 $X.XX \pm 0.25$
3. TERM. NOS. FOR REF. ONLY
4. RATING: 20A 125VAC, 16A 250VAC UL APPROVED
5. ELECTRICAL LIFE: OVER 10,000 CYCLES
6. MECHANICAL LIFE: OVER 30,000 CYCLES
7. CONTACT RESISTANCE:  $<20 \text{ m}\Omega$  (INITIAL)
8. DIELECTRIC STRENGTH:  $>1500\text{V } 1 \text{ min}$
9. INSULATION RESISTANCE:  $>1,000 \text{ m}\Omega @ 500\text{V DC}$
10. OPERATING TEMPERATURE: TERMINAL SIDE  $-20^{\circ}\text{C}$  to  $85^{\circ}\text{C}$   
ROCKER SIDE  $-20^{\circ}\text{C}$  to  $55^{\circ}\text{C}$
11. ▲ DENOTES CRITICAL PARAMETER



|                                                                                                              |            |                                 |          |    |                                                                                                            |                   |          |                |          |           |
|--------------------------------------------------------------------------------------------------------------|------------|---------------------------------|----------|----|------------------------------------------------------------------------------------------------------------|-------------------|----------|----------------|----------|-----------|
| REV                                                                                                          | ECO NO     | DESCRIPTION                     | DATE     | BY | <div> E-SWITCH®</div> |                   |          |                |          | OBJECT ID |
| K                                                                                                            | ECO-100468 | REMOVE VDE/ENEC RATING AND LOGO | 01/24/22 | JS |                                                                                                            |                   |          |                |          | 000016372 |
|                                                                                                              |            |                                 |          |    | TITLE R4FBLKBLKEF0                                                                                         |                   |          |                |          |           |
|                                                                                                              |            |                                 |          |    |                                                                                                            |                   |          |                |          |           |
| THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED |            |                                 |          |    | SCALE<br>1:1                                                                                               | DATE<br>3/30/1999 | DR<br>MM | DWG<br>M040109 | REV<br>K |           |