

Power Driving


- Chrome vanadium alloy steel
- Anti-rust oiled, sand-blasted

1/4" Hex size shank driver



75A1


- Threaded rod socket
- Fastest tool available to tighten or loosen threaded rods
- Automatic locking cams
- Will not damage the threads when used properly



KT NO.	Size mm inch	D mm	L mm	Capacity Ø mm	g	kg
75A105M	5 3/16	22	66	4.6~5.0	60	10 / 72
75A106M	6 1/4	24	66	5.6~6.35	75	10 / 80
75A108M	8 5/16	24	66	7.6~8.0	74	10 / 80
75A110M	10 3/8	28	66	9.0~10.0	99	10 / 107
75A112M	12 1/2	28	66	11.4~12.7	98	10 / 103
75A114M	14 9/16	32	66	13.2~14.3	126	10 / 127
75A116M	16 5/8	32	66	15.2~16.0	125	10 / 125

760M

- Nut setter
- Non magnetic type
- DIN 3126



760S




KT NO.	mm	ℓ mm	Overall length (mm)	g	kg
7605512M	12	7.0	55	55	6 / 72
7606512M	12	6.8	65	50	6 / 72
7607510M	10	6.0	75	38	6 / 72

KT NO.	mm	ℓ mm	Overall length (mm)	g	kg
7601012M	12	7.5	100	61	1 / 25
7601013M	13	7.0	100	70	1 / 25

KT NO.	inch	ℓ mm	Overall length (mm)	g	kg
7606508S	1/4	4.8	65	20	6 / 84
7606510S	5/16	6.6	65	30	6 / 84
7606512S	3/8	6.8	65	36	6 / 72

761M

- Nut setter
- Magnetic type
- DIN 3126



761S



KT NO.	mm	ℓ mm	Overall length (mm)	g	kg
7616505M	5	2.3	65	27	6 / 84
7616506M	6	2.6	65	26	6 / 84
7616507M	7	2.9	65	25	6 / 84
7616508M	8	3.5	65	30	6 / 84
7616510M	10	4.5	65	37	6 / 72
7616512M	12	5.6	65	52	6 / 72
7616513M	13	6.0	65	54	6 / 72
7616514M	14	6.5	65	52	6 / 20

KT NO.	mm	ℓ mm	Overall length (mm)	g	kg
7611006M	6	2.6	100	38	1 / 25
7611008M	8	3.5	100	48	1 / 25
7611010M	10	4.5	100	54	1 / 25
7611012M	12	5.6	100	68	1 / 25
7611013M	13	6.0	100	71	1 / 25
7611014M	14	6.5	100	77	1 / 25
7611506M	6	2.6	150	58	1 / 25
7611507M	7	2.9	150	65	1 / 25
7611508M	8	3.5	150	67	1 / 25
7611510M	10	4.5	150	68	1 / 25
7611512M	12	5.6	150	103	1 / 25
7611513M	13	6.0	150	110	1 / 25
7611514M	14	6.5	150	115	1 / 25
7612006M	6	2.6	200	78	1 / 20
7612008M	8	3.5	200	93	1 / 20
7612010M	10	4.5	200	89	1 / 20
7612012M	12	5.6	200	128	1 / 20
7612014M	14	6.5	200	128	1 / 20

KT NO.	inch	ℓ mm	Overall length (mm)	g	kg
7614208S	1/4	2.7	42	15	6 / 84
7614210S	5/16	3.7	42	17	6 / 84
7614512S	3/8	4.7	45	22	6 / 84
7616508S	1/4	4.8	65	30	6 / 84
7616510S	5/16	6.6	65	31	6 / 84
7616512S	3/8	6.8	65	37	6 / 72
7616514S	7/16	6.8	65	39	6 / 72