






O.P. (MM)	P.T. (MM)
7.00 ± 0.2	0.35

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X ± 0.4
X.XX ± 0.25
- ▲ 3. RATING: 0.1A @ 5VDC
4. OPERATING FORCE: 70 ± 20 GRAMS
- ▲ 5. OPERATING TEMP: -25°C TO 75°C
6. ELECTRICAL LIFE: 10,000 CYCLES MIN.
7. INSULATION RESISTANCE: 100 MEGA-OHMS MIN.
8. DIELECTRIC STRENGTH: 500VAC - 1 MINUTE
9. ▲ DENOTES CRITICAL PARAMETER.
10. 2011/65/EU (ROHS) COMPLIANT



A	23039	NEW RELEASE	10/11/17	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE SS075Q100F070R1A

SCALE 4:1	DATE 10/11/2017	DR MJR	DWG Q971042	REV A
--------------	--------------------	-----------	----------------	----------