









O.P. (MM)	P.T. (MM)
9.1 ± 0.8	4.4 MAX

O.P. = OPERATING POINT
P.T. = PRE-TRAVEL



NOTES:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- RATING: 5A @125/250VAC UL, CUL APPROVED
- ▲ OPERATING FORCE: 25± 12 GRAMS
- OPERATING TEMP: -25°C to 85°C
- ELECTRICAL LIFE: 50,000 CYCLES MIN.
- MECHANICAL LIFE: 1,000,000 CYCLES TYP.
- INSULATION RESISTANCE: 100 MΩ
- DIELECTRIC STRENGTH: 1000VAC 1 MINUTE (INITIAL VALUE)
- CONTACT RESISTANCE: 100 MILLI-OHMS MAX.
- ▲ DENOTES CRITICAL PARAMETER.



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-100799	REMOVE VDE RATING AND LOGO	03/24/22	JS	MS0850502F025V1A				000021297
					TITLE				
					SCALE	DATE	DR	DWG	REV
					2:1	1/30/2017	MW	Q970163	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED