






▲ CIRCUIT: SPST



NOTES

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: $X.X = \pm 0.4$
 $X.XX = \pm 0.25$
3. TERMINAL NUMBERS FOR REF. ONLY.
- ▲ 4. OPERATING FORCE: $300 \pm 50\text{gf}$
5. OPERATING LIFE: 1,000,000 CYCLES
6. TRAVEL: $0.5 \pm 0.15\text{mm}$
7. CONTACT RATING: 12VDC @ 50mA
8. CONTACT RESISTANCE: $100\text{m}\Omega$ MAX
9. INSULATION RESISTANCE: $100\text{M}\Omega$ MIN @ 100VDC.
- ▲ 10. CONTACT MATERIAL: SILVER
11. OPERATING TEMPERATURE: -40°C TO 85°C
12. PACKAGING: TAPE & REEL, 700 PCS. PER REEL
13. ▲ DENOTES CRITICAL PARAMETER
14. 2002/95/EC (ROHS) COMPLIANT



A	21882	INITIAL RELEASE	6/17/2015	MW	TITLE TL6120BF300QG				
REV	PCR NO	DESCRIPTION	DATE	BY					
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 4:1	DATE 6/17/2015	DR MW	DWG T351514	REV A