

UNIVERSAL DRILL STAND

For precision and safety drilling. Working surface with clamping grooves for fastening clamping blocks or vices

50.020	with rotary collar ø 43 mm - height 420 mm - stroke 60 mm - depth 96 mm - working height 240 mm - column ø 22 mm - with return spring - aluminium base 220 x 175 mm	1	500201
50.030	with rotary collar ø 60 mm - with 3 reducing collars ø 43-50-53 mm - height 500 mm - stroke 65 mm - depth 95 mm - working height 320 mm - column ø 30 mm - with return spring - aluminium base 250 x 180 mm - professional model	1	500300
50.040	with rotary collar ø 60 mm - with 3 reducing collars ø 43-50-53 mm - height 500 mm - stroke 65 mm - depth 95 mm - working height 320 mm - column ø 30 mm - with return spring - cast iron base 250 x 180 mm - professional model	1	500409

**REDUCING COLLAR** for drill stands

43.034	ø 43 x 34 mm	1	430348
43.037	ø 43 x 37 mm	1	430379
43.038	ø 43 x 38 mm	1	430386
43.384	ø 43 x 38,4 mm	1	433844
60.043	ø 60 x 43 mm	1	600437
60.046	ø 60 x 46 mm	1	600468
60.050	ø 60 x 50 mm	1	600505
60.053	ø 60 x 53 mm	1	600536
60.054	ø 60 x 54 mm	1	600543
60.056	ø 60 x 56 mm	1	600567

