






PANEL THICKNESS	X
0.70-1.25	19.1-19.2
1.25-2.00	19.3-19.4
2.00-3.00	19.4-19.6



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. RATING: 6A @250VAC (cURus)
9A @125VAC (cURus)
4(1)A @250VAC (VDE)
- ▲ 4. LAMP VOLTAGE: 12VDC (LED)
5. MATERIAL:
CONTACT SURFACE: COIN SILVER, SILVER PLATE
TERMINAL: COPPER ALLOY W/SILVER PLATE.
6. CONTACT RESISTANCE: $< 20\text{m}\Omega$
7. INSULATION RESISTANCE: 1000M Ω
8. DIELECTRIC STRENGTH: $> 1500\text{V RMS min. @SEA LEVEL}$
9. MECHANICAL LIFE: 30,000 CYCLES
10. ELECTRICAL LIFE: 10,000 CYCLES
11. ▲ DENOTES CRITICAL PARAMETER.



D	24415	update print	7/23/20	MW
C	24216	Incandescent Bulb to LED	3/9/20	MW
B	22655	Add ON - OFF to circuit diagram	12/29/16	MW
A	18434	RELEASED FOR PRODUCTION	3/23/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE R1973ABLKGILGF3

SCALE 3:2

DATE 3/23/2009

DR TN

DWG M400402

REV D