



## USB Cable

Model: **AK-USB-38**



|                          |                           |
|--------------------------|---------------------------|
| Product code             | AK-USB-38                 |
| Product type             | USB Cable                 |
| Maximum power            | 100 W (20 V / 5 A)        |
| Cable length             | 1.8 m                     |
| The cable plug #1        | USB Male connector type C |
| The cable plug #2        | USB Male connector type C |
| Data transmission        | 480 Mbps                  |
| Plated plugs             | Yes - nickel plated       |
| Product color            | Blue                      |
| Package                  | UniBag                    |
| Product size (L x W x H) | 150 x 100 x 10 mm         |
| Package size (L x W x H) | 180 x 130 x 11 mm         |
| Net weight               | 58 g                      |
| Gross weight             | 63 g                      |
| RoHS compatibility       | Yes                       |
| REACH compatibility      | Yes                       |
| EAN code                 | 5901720137524             |
| Warranty                 | 24 months                 |



# Description

**The Akyga AK-USB-38 USB-C cable** has been created for fast charging of devices with **100 watts** of power. It is a high-quality **1.8 m cable** terminated on both sides with **USB Type C plugs**. These connectors are compatible with most mobile devices available on the market. Thus, you can charge both your smartphone, wireless headphones, keyboard and laptop with a single cable. Thus, the USB-C cable will solve most of the problems associated with tangled cables in your drawer. What's more, the USB plugs are equipped with a special **E-Mark chip**. It is responsible for adapting the power parameters to the currently connected device. It is essential for achieving maximum charging power with Power Delivery chargers. The cable is compatible with chargers equipped with Power Delivery (PD), Quick Charge (QC), as well as Samsung (AFC), Huawei (FCP/SCP), or Apple (2.4 A).