


RECOMMENDED PANEL CUTOUT

PANEL THICKNESS	(x)
0.75 - 1.25	30.0
1.25 - 2.00	30.2
2.00 - 3.00	30.5




SWITCH FUNCTION	
POS. 1	POS. 2
	
ON	ON
2-3, 5-6	2-1, 5-4



CIRCUIT: DPDT

NOTE:

1. DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
4. CONTACT MATERIAL: SILVER
5. CONTACT RATINGS: 16A @ 125/250VAC [cURus]
20A @ 125/250VAC [cURus]
1/3HP 125/250VAC T105 [cURus]
3/4HP 125/250VAC T105 [cURus]
6. CONTACT RESISTANCE: 20m Ω MAX. INITIAL
7. INSULATION RESISTANCE: 100M Ω MIN. @ 500VDC
8. DIELECTRIC STRENGTH: 1,000VAC FOR 1 MINUTE
9. ELECTRICAL LIFE: 6,000 CYCLES [cURus]
10. OPERATING TEMPERATURE: -20°C to 55°C [cURus]
11. ▲ DENOTES CRITICAL PARAMETER
- ▲ 12. ILLUMINATION: NON-ILLUMINATED



REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH® OBJECT ID 000000311				
B	ECO-100605	REMOVE VDE/ENEC RATING AND LOGO	01/04/22	JS					
					TITLE RB24GD1121				
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE 1:1	DATE 8/4/2020	DR MW	DWG 14-RB24GD1121	REV B