





NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY.
4. RATING: 50mA @ 12VDC
5. TRAVEL: 0.30 ± 0.15 mm
6. OPERATING FORCE: 260 ± 50 gf
7. CONTACT RESISTANCE: 100 mILLI-OHMS MAX.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.



B	23662	drawing update to round corners	11/8/18	MW
A	23282	NEW RELEASE	3/23/18	MJR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



E-SWITCH®

TITLE TL1100F260Q5JBLK

SCALE
3:1DATE
3/23/2018DR
MJRDWG
XP0282PREV
B