








RECOMMENDED P.C.B. LAYOUT



▲ SCHEMATIC

## NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50mA @12VDC
5. TRAVEL: 0.25 +0.2/-0.1mm
6. CONTACT RESISTANCE: 100MILLI-OHMS Max.
- ▲ 7. OPERATING FORCE: 180  $\pm 50$ gf
- ▲ 8. CONTACT MATERIAL: SILVER
- ▲ 9. MATERIAL - HOUSING AND ACTUATORS: UL94-V0
10. PACKAGING: 600 per TRAY
11. ▲ DENOTES CRITICAL PARAMETER.



| REV | ECO NO     | DESCRIPTION  | DATE     | BY | E-SWITCH®    |            |     |         | OBJECT ID |
|-----|------------|--------------|----------|----|--------------|------------|-----|---------|-----------|
| P   | ECO-100677 | update notes | 01/19/22 | MW | TITLE TL2243 |            |     |         | 000017801 |
|     |            |              |          |    | SCALE        | DATE       | DR  | DWG     | REV       |
|     |            |              |          |    | 4:1          | 10/10/2008 | BLR | P010405 | P         |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED