


 $17.60^{+.20}_{-.00}$
[.69^{+.008}_{-.000} in]

 $\varnothing 19.00^{+.20}_{-.00}$
[$\varnothing 19.00^{+.008}_{-.000}$ in]

 $\varnothing 15.50$
[.61 in]

 $\varnothing 22.00$
[.87 in]


▲ POWER SYMBOL
ILLUMINATION
Bi-COLOR:
RED / GREEN

▲ ACTUATOR
BLACK ANODIZED





NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A 250 VAC cUL
6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES
AT FULL LOAD.
7. MECHANICAL LIFE: 500,000 CYCLES.
8. INSULATION RESISTANCE: 1,000 M Ω @ 500VDC MIN.
9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
10. CONTACT RESISTANCE: 50m Ω MAX. @ 1A 12VDC
11. OPERATING TEMP: -20°C to 55°C
12. ▲ DENOTES CRITICAL PARAMETER.
- ▲ 13. LAMP VOLTAGE: 20mA 3V
14. TRAVEL: 3.2mm
15. ACTUATION FORCE: 3.5 $\pm$ 1.0 N
16. MOUNTING NUT TORQUE: 5-14 Nm
17. INGRESS PROTECTION: IP67
18. HARDWARE SUPPLIED: O-RING AND HEXNUT



▲ HOUSING
BLACK ANODIZED



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-100336	UPDATE PANEL CUTOUT	12/09/21	JS	TITLE ULV4F2G115G1				000026050
					SCALE	DATE	DR	DWG	REV
					3:2	3/15/2016	MW	T940048	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED