






RoHS compliant



PCB Layout
tolerances ± 0.1

MATERIALS

- Insulator: Thermoplastic UL 94-V-0 white
- Contact: Machined / Copper alloy
- Contact finish: Quality class 2
- Shell: steel tin plated

CHARAKTERISTICS

- Working voltage: 60V
- Current rating: 5A
- Contact resistance: max. $10\text{m}\Omega$ - DIN41652
- Insulation resistance: $>5\text{G}\Omega$
- Temperature range: -55° to $+125^\circ\text{C}$

General tolerances (Deltron standard)				
size in mm		tolerances		
> 0.5 up to 3	> 3 up to 6	> 6 up to 30	> 30 up to 120	
±0.1	±0.2	±0.2	±0.3	

modification	Rev. a) 13.12.09 mr	Rev.	Rev.	DE010773		
	Rev.	Rev.	Rev.	part no.		
HD-D44SY/2			1.5:1	drawn	30.01.2009	mr
			scale	checked		
				approved		
DELTRON SWISS CONNECT 2 CUSTOMIZE			Industrie Neuhof 8c CH-3422 Kirchberg www.d-sub.swiss			
			K060405 a drawing no.			