

**HSS ENLARGING CUTTER** for steel

|               |                                                                                                                      |   |        |
|---------------|----------------------------------------------------------------------------------------------------------------------|---|--------|
| <b>800.00</b> | from $\varnothing$ <b>3</b> mm to $\varnothing$ <b>14</b> mm -<br>shank $\varnothing$ <b>6</b> mm - <b>550</b> RPM   | 1 | 800004 |
| <b>805.00</b> | from $\varnothing$ <b>6</b> mm to $\varnothing$ <b>20</b> mm -<br>shank $\varnothing$ <b>8</b> mm - <b>500</b> RPM   | 1 | 805009 |
| <b>810.00</b> | from $\varnothing$ <b>8</b> mm to $\varnothing$ <b>30</b> mm -<br>shank $\varnothing$ <b>10</b> mm - <b>400</b> RPM  | 1 | 810003 |
| <b>820.00</b> | from $\varnothing$ <b>20</b> mm to $\varnothing$ <b>40</b> mm -<br>shank $\varnothing$ <b>10</b> mm - <b>300</b> RPM | 1 | 820002 |
| <b>825.00</b> | from $\varnothing$ <b>20</b> mm to $\varnothing$ <b>50</b> mm -<br>shank $\varnothing$ <b>10</b> mm - <b>200</b> RPM | 1 | 825007 |

**HSS STEP DRILL BIT** for steel

|               |                                                                                                                       |   |        |
|---------------|-----------------------------------------------------------------------------------------------------------------------|---|--------|
| <b>825.50</b> | from $\varnothing$ <b>4</b> mm to $\varnothing$ <b>12</b> mm -<br>shank $\varnothing$ <b>6</b> mm - <b>800</b> RPM    | 1 | 825502 |
| <b>826.00</b> | from $\varnothing$ <b>4</b> mm to $\varnothing$ <b>20</b> mm -<br>shank $\varnothing$ <b>8</b> mm - <b>500</b> RPM    | 1 | 826004 |
| <b>828.00</b> | from $\varnothing$ <b>4</b> mm to $\varnothing$ <b>30</b> mm -<br>shank $\varnothing$ <b>10</b> mm - <b>400</b> RPM   | 1 | 828008 |
| <b>829.00</b> | from $\varnothing$ <b>3,5</b> mm to $\varnothing$ <b>40</b> mm -<br>shank $\varnothing$ <b>10</b> mm - <b>300</b> RPM | 1 | 829005 |

