



PRODUCT-DETAILS

TY527MR

CBL TIE 120LB 13IN NATURAL NYLON



General Information

Extended Product Type	TY527MR
Product ID	7TCG009310R0017
EAN	5414363065852
Catalog Description	CBL TIE 120LB 13IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 343mm (13.5 Inches), Width of 6.9mm (0.27 Inch), Thickness of 1.5mm (0.06 Inches), Tensile Strength Rating of 540 Newtons (120 Pounds), Euroslot Packaging

Ordering

E-Number (Finland)	1370039
EAN	5414363065852
UPC	786210518817
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.27 in 7 mm
Product Net Depth / Length	13.4 in 340 mm

Container Information

Package Level 1 Units	50 piece
Package Level 2 Units	2000 piece
Package Level 2 Width	16 in 406 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	23 in 584 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	TY-RAP FASTENING
Product Type	High Performance
RoHS Date	9AKK107991A8366
Tensile Strength	120 lb 540 N
Thickness	0.06 in 1.65 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000487
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY527MR
REACH Declaration	9AKK107992A8781
RoHS Information	9AKK107991A8366

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

