



PRODUCT-DETAILS

TYB24M

CABLE TIE 30LB 5.5IN NAT NYL WKBOX



General Information

Extended Product Type	TYB24M
Product ID	7TCG009140R0019
EAN	5414363067054
Catalog Description	CABLE TIE 30LB 5.5IN NAT NYL WKBOX
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 139.7mm (5.5 Inches), Width of 3.56mm (0.14 Inches), Thickness of 1.31mm (0.052 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), Workbench Box Packaging

Ordering

EAN	5414363067054
UPC	786210530185
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.14 in 3.56 mm
Product Net Depth / Length	5.5 in 139.7 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	5.3 in 135 mm
Package Level 1 Height	5.3 in 135 mm
Package Level 1 Depth / Length	5.3 in 135 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	11.8 in 300 mm
Package Level 2 Height	6.3 in 160 mm
Package Level 2 Depth / Length	29.1 in 739 mm

Technical UL/CSA

Flammability According to UL 94	V-2
---------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	PLASTIC CABLE TIE
Product Type	High Performance
Standards	UL E49405
Tensile Strength	40 lb 180 N
Thickness	0.05 in 1.31 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TYB24M
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TYB24M
REACH Declaration	9AKK107992A8781
RoHS Information	9AKK107991A8366

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

