

PRODUCT-DETAILS

TYHB23M

CABLE TIE 18LB 4IN GR NYL HEAT STBL



General Information

Extended Product Type	TYHB23M
Product ID	7TCG009460R0111
EAN	5414363067511
Catalog Description	CABLE TIE 18LB 4IN GR NYL HEAT STBL
Long Description	Cable Tie, Heat Stabilized Natural Polyamide (Nylon 6.6) for Temperatures up to 105 Degrees Celsius (220 F), Weather and Ultra-Violet Resistant for Indoor and Outdoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 92mm (3.6 Inches), Width of 2.3mm (0.09 Inches), Thickness of 1.0mm (0.04 Inches), Tensile Strength Rating of 80 Newtons (18 pounds)

Ordering

EAN	5414363067511
UPC	786210511993
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.09 in 2.4 mm
Product Net Depth / Length	3.62 in 92 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 2 Units	10000 piece
Package Level 2 Width	9.4 in 239 mm
Package Level 2 Height	4.7 in 119 mm
Package Level 2 Depth / Length	22.8 in 579 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.06 to 0.63 in 1.5 to 16 mm
Color	Natural
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	TY-RAP FASTENING
Product Type	Heat-Stabilized
RoHS Date	9AKK108466A3874
Tensile Strength	18 lb 80 N
Thickness	0.04 in 1 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000494
Instructions and Manuals	TYHB23M
REACH Declaration	9AKK108466A3877
RoHS Information	9AKK108466A3874

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

