


24V dual signal digital RGB LED Strip 120LEDs/m



Product Description:

digital 24V LED Strip with 120pcs SMD2835 RGB

Dual signal line transmission and Break point resume

The strip will keep working if any LED becomes damaged or physically removed

20Pixels/m, IC Tm1934 cut-able every 50mm

DC24V voltage, the voltage drop will be less

White PCB, PCB wide is 10mm


5 Meters per reel, customized sizes are also available

4Pin JST SM connector, IP Rate: IP20, IP64, IP65

Product Datasheet

Product Number	S010120BC3SE0	Luminance/M	R: 18lm G: 56lm B: 18lm
Operating Voltage	DC24V	Ra	/
Power/M	24W	Beam Angle	120°
SMD Type	SMD 2835	Size (mm)	5000 * 10mm
LED Qty/M	120	IP Rate	IP20/IP64/IP65
Color	RGB	Operation Temperature	- 25 ~ 60 °C
Pixel/M	20	Material	FPC
Control	TM1934	Cutting Length	50mm
Wavelength	R:620-625 G:520-525 B:460-465nm	Net Weight/Roll	0.13KG


Outline Dimension (unit: mm)




◆ Order number

DC24V	RGB	White PCB	IP20	S010120BC3SE0/C1
DC24V	RGB	White PCB	IP65	S010120BC3SE0/C2

◆ Wiring diagram



◆ Strip IP Rate



◆ Accessories



Screw



Silicone clip



End cap

Note: The parameters are subject to change without notice!