

# Test Probe

## GKS-100 313 090 A 2000

Item GKS-100-0323



**ingun**<sup>®</sup>

Partner for Future Technology

- Well-established test probes for contacting PCBs
- For optimal contact to the test points (e.g. pads, vias, and pins), various tip styles with various diameters and finishes are available.
- Various spring forces available as well as versions with stainless steel springs suitable for high temperatures
- Used for setting the optimum stroke conditions in the test fixture, various installation heights can be achieved by combining test probes and receptacles

### INGUN SELECTION

#### General data

|                                |                                               |
|--------------------------------|-----------------------------------------------|
| Product group                  | ICT / FCT (in-circuit test and function test) |
| Sub-product group              | Standard stroke test probe                    |
| Series                         | GKS-100                                       |
| Grid                           | 2.54 mm [100 mil]                             |
| Contacting from                | Pad, Female connector                         |
| Magnetic                       | Yes                                           |
| Installation type              | Plug-in                                       |
| Quick-exchange system          | Yes                                           |
| Adjustable installation height | No                                            |
| Non-rotating                   | No                                            |
| Compatible receptacle(s)       | KS-100                                        |
| Min. temperature               | - 40 °C [- 104 °F]                            |
| Max. temperature               | + 80 °C [+ 176 °F]                            |
| RoHS-compliant                 | Yes                                           |

#### Electrical data


|                                       |          |
|---------------------------------------|----------|
| Current load capacity / rated current | 8 A      |
| Typical resistance (Ri)               | <20 mOhm |

#### Mechanical data

|                                |                   |
|--------------------------------|-------------------|
| Total length                   | 33.4 mm [1.31 in] |
| Barrel diameter                | 1.37 mm [.053 in] |
| Maximum stroke                 | 6.35 mm [.25 in]  |
| Spring pre-load                | 0.66 N [2.37 ozf] |
| Collar height                  | 00                |
| Spring force at working stroke | 2 N [7.19 ozf]    |
| Recommended working stroke     | 4.3 mm [.169 in]  |

#### Tip style data


|                    |                            |
|--------------------|----------------------------|
| Tip style          | 13 30° needle tip, rounded |
| Tip diameter       | 0.9 mm [.035 in]           |
| Tip style surface  | A gold                     |
| Tip style material | 3 CuBe                     |



Test Probe  
**GKS-100 313 090 A 2000**  
Item GKS-100-0323



**ingun**<sup>®</sup>  
Partner for Future Technology



**INGUN Prüfmittelbau GmbH**

Max-Stromeyer-Straße 162  
78467, Constance, Germany  
Phone +49 7531 8105-0  
Customer hotline +49 7531 8105-888  
Fax +49 7531 8105-65  
info@ingun.com



Prices and delivery times on request.  
Technical changes reserved. 11/22 EN

Weitere Informationen zum Thema  
**Test probes**

