


Hexalobular (6 Lobe) socket button head screws with collar fully threaded

BN 20367



Additional information	Fasteners to the given specification have a reduced loadability due to the head geometry according to ISO 898-1.
Headform	Button with collar
Drive	Hexalobular socket
Thread	fully threaded
Material	Steel
Strength class	08.8
Surface	zinc plated blue
Standard	~ISO 7380-2

Article no.	d1	L	d2 max.	d3~	k max.	c~	a max.	Hexalobular socket	t max.	A~
3487103	M3	6	7	5,3	1,7	0,7	1	X10	1,15	2,8
3487105	M3	8	7	5,3	1,7	0,7	1	X10	1,15	2,8
3487106	M3	10	7	5,3	1,7	0,7	1	X10	1,15	2,8
3487107	M3	12	7	5,3	1,7	0,7	1	X10	1,15	2,8
3487108	M3	16	7	5,3	1,7	0,7	1	X10	1,15	2,8
3487110	M3	20	7	5,3	1,7	0,7	1	X10	1,15	2,8
3487111	M4	6	9,4	7,3	2,2	0,8	1,4	X20	1,5	3,95
3487112	M4	8	9,4	7,3	2,2	0,8	1,4	X20	1,5	3,95
3487113	M4	10	9,4	7,3	2,2	0,8	1,4	X20	1,5	3,95
3487115	M4	12	9,4	7,3	2,2	0,8	1,4	X20	1,5	3,95
3487116	M4	16	9,4	7,3	2,2	0,8	1,4	X20	1,5	3,95
3487117	M4	20	9,4	7,3	2,2	0,8	1,4	X20	1,5	3,95
3487118	M4	25	9,4	7,3	2,2	0,8	1,4	X20	1,5	3,95
3487119	M5	8	11,6	9,2	2,8	1	1,6	X25	1,9	4,5

Article no.	d1	L	d2 max.	d3~	k max.	c~	a max.	Hexalobular socket	t max.	A~
3487120	M5	10	11,6	9,2	2,8	1	1,6	X25	1,9	4,5
3487121	M5	12	11,6	9,2	2,8	1	1,6	X25	1,9	4,5
3487122	M5	16	11,6	9,2	2,8	1	1,6	X25	1,9	4,5
3487123	M5	20	11,6	9,2	2,8	1	1,6	X25	1,9	4,5
3487124	M5	25	11,6	9,2	2,8	1	1,6	X25	1,9	4,5
3487125	M5	30	11,6	9,2	2,8	1	1,6	X25	1,9	4,5
3487126	M6	8	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487127	M6	10	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487128	M6	12	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487129	M6	16	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487130	M6	20	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487131	M6	25	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487132	M6	30	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487133	M6	35	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487134	M6	40	13,7	10,2	3,3	1,1	2	X30	2,1	5,6
3487135	M8	10	17,8	13,7	4,4	1,5	2,5	X40	2,7	6,75
3487137	M8	12	17,8	13,7	4,4	1,5	2,5	X40	2,7	6,75
3487138	M8	16	17,8	13,7	4,4	1,5	2,5	X40	2,7	6,75
3487139	M8	20	17,8	13,7	4,4	1,5	2,5	X40	2,7	6,75
3487140	M8	25	17,8	13,7	4,4	1,5	2,5	X40	2,7	6,75
3487141	M8	30	17,8	13,7	4,4	1,5	2,5	X40	2,7	6,75
3487142	M8	35	17,8	13,7	4,4	1,5	2,5	X40	2,7	6,75
3487143	M8	40	17,8	13,7	4,4	1,5	2,5	X40	2,7	6,75
3487144	M10	16	22	17,5	5,5	1,7	3	X45	3,4	7,9
3487145	M10	20	22	17,5	5,5	1,7	3	X45	3,4	7,9
3487146	M10	25	22	17,5	5,5	1,7	3	X45	3,4	7,9
3487148	M10	30	22	17,5	5,5	1,7	3	X45	3,4	7,9
3487149	M10	35	22	17,5	5,5	1,7	3	X45	3,4	7,9
3487150	M10	40	22	17,5	5,5	1,7	3	X45	3,4	7,9
3487153	M12	20	25	21	7	2,4	3,5	X50	4,2	8,95
3487154	M12	25	25	21	7	2,4	3,5	X50	4,2	8,95
3487156	M12	30	25	21	7	2,4	3,5	X50	4,2	8,95
3487158	M12	35	25	21	7	2,4	3,5	X50	4,2	8,95
3487159	M12	40	25	21	7	2,4	3,5	X50	4,2	8,95
3487160	M12	45	25	21	7	2,4	3,5	X50	4,2	8,95
3487161	M12	50	25	21	7	2,4	3,5	X50	4,2	8,95