

Stroke Measurement Probe

HMS-100 305 090 A

Item HMS-100-0001



ingun[®]

Partner for Future Technology

INGUN SELECTION



1:1

Stroke Measurement Probe

HMS-100 305 090 A

Item HMS-100-0001



GO TO PRODUCT

ingun[®]


Partner for Future Technology

General data

Product group
Sub-product group
Series
Grid
Contacting from
Magnetic
Installation type
Quick-exchange system
Adjustable installation height
Non-rotating
Compatible receptacle(s)
Min. temperature
Max. temperature
RoHS-compliant

Accessories (GKS / ADA)
Stroke-measuring probe
HMS-100
2.54 mm [100 mil]
Pad, Female connector
Yes
Plug-in
Yes
No
No
KS-100
- 40 °C [- 104 °F]
+ 80 °C [+ 176 °F]
Yes

INGUN SELECTION



Mechanical data

Total length
Barrel diameter
Maximum stroke
Collar height
Recommended working stroke

33.4 mm [1.31 in]
1.37 mm [0.053 in]
6.35 mm [0.25 in]
00
4.3 mm [0.169 in]

Tip style data

Tip style
Tip diameter
Tip style surface
Tip style material

05 bullet-nosed (full radius)
0.9 mm [0.035 in]
A gold
3 CuBe

INGUN Prüfmittelbau GmbH

Max-Stromeyer-Straße 162
78467, Constance, Germany
Phone +49 7531 8105-0
Customer hotline +49 7531 8105-888
Fax +49 7531 8105-65
info@ingun.com



Prices and delivery times on request.
Technical changes reserved. 11/22 EN

Weitere Informationen zum Thema
Test probes

