


Hexalobular (6 Lobe) socket head cap screws with low head, fully threaded

BN 4850



Standard	ISO 14580,
Additional information	Fasteners to the given specification have a reduced loadability due to the head geometry according to ISO 898-1.
Headform	Cylindrical low
Drive	Hexalobular socket
Thread	fully threaded
Material	Steel
Property class	08.8
Surface	zinc plated blue

Article no.	d1	L	d2 max.	k max.	Hexalobular socket	t max.	A~
3645891	M3	4	5,5	2,4	X10	1,27	2,8
3271425	M3	5	5,5	2,4	X10	1,27	2,8
1145924	M3	6	5,5	2,4	X10	1,27	2,8
1145932	M3	8	5,5	2,4	X10	1,27	2,8
1145940	M3	10	5,5	2,4	X10	1,27	2,8
1145959	M3	12	5,5	2,4	X10	1,27	2,8
1145967	M3	16	5,5	2,4	X10	1,27	2,8
3055575	M3	20	5,5	2,4	X10	1,27	2,8
3271426	M3	25	5,5	2,4	X10	1,27	2,8
3271428	M3	30	5,5	2,4	X10	1,27	2,8
3645893	M3	40	5,5	2,4	X10	1,27	2,8
3645892	M3	45	5,5	2,4	X10	1,27	2,8
3645894	M4	5	7	3,1	X20	1,66	3,95
1145975	M4	6	7	3,1	X20	1,66	3,95

Article no.	d1	L	d2 max.	k max.	Hexalobular socket	t max.	A~
1145983	M4	8	7	3,1	X20	1,66	3,95
1145991	M4	10	7	3,1	X20	1,66	3,95
1146009	M4	12	7	3,1	X20	1,66	3,95
1146017	M4	16	7	3,1	X20	1,66	3,95
1146025	M4	20	7	3,1	X20	1,66	3,95
3055576	M4	25	7	3,1	X20	1,66	3,95
3271429	M4	30	7	3,1	X20	1,66	3,95
3645895	M4	35	7	3,1	X20	1,66	3,95
3645896	M4	40	7	3,1	X20	1,66	3,95
3645897	M4	45	7	3,1	X20	1,66	3,95
3645898	M4	50	7	3,1	X20	1,66	3,95
1146033	M5	8	8,5	3,65	X25	1,91	4,5
1146041	M5	10	8,5	3,65	X25	1,91	4,5
1146068	M5	12	8,5	3,65	X25	1,91	4,5
1146076	M5	16	8,5	3,65	X25	1,91	4,5
1146084	M5	20	8,5	3,65	X25	1,91	4,5
1146092	M5	25	8,5	3,65	X25	1,91	4,5
3055577	M5	30	8,5	3,65	X25	1,91	4,5
3645899	M5	35	8,5	3,65	X25	1,91	4,5
3645900	M5	40	8,5	3,65	X25	1,91	4,5
3645901	M5	45	8,5	3,65	X25	1,91	4,5
3645902	M5	50	8,5	3,65	X25	1,91	4,5
3645903	M6	6	10	4,4	X30	2,29	5,6
1146106	M6	8	10	4,4	X30	2,29	5,6
1146114	M6	10	10	4,4	X30	2,29	5,6
1146122	M6	12	10	4,4	X30	2,29	5,6
1146130	M6	16	10	4,4	X30	2,29	5,6
1146149	M6	20	10	4,4	X30	2,29	5,6
1146157	M6	25	10	4,4	X30	2,29	5,6
1146165	M6	30	10	4,4	X30	2,29	5,6
3271430	M6	35	10	4,4	X30	2,29	5,6
3055578	M6	40	10	4,4	X30	2,29	5,6
3645904	M6	45	10	4,4	X30	2,29	5,6
3645905	M6	50	10	4,4	X30	2,29	5,6
1146173	M8	10	13	5,8	X45	3,05	7,95
1146181	M8	12	13	5,8	X45	3,05	7,95
1146203	M8	16	13	5,8	X45	3,05	7,95
1146211	M8	20	13	5,8	X45	3,05	7,95
1146238	M8	25	13	5,8	X45	3,05	7,95
1146246	M8	30	13	5,8	X45	3,05	7,95
3271431	M8	35	13	5,8	X45	3,05	7,95
1146254	M8	40	13	5,8	X45	3,05	7,95
3055579	M8	50	13	5,8	X45	3,05	7,95