

1

2

3

4

5

6

7

FOR
客户名称APPROVED
客户确认签字ATTN
销售负责人

A

B

C

D

E





A

B


C

D

E



SCHEMATIC



PART NUMBER: ONPOW6116F-11■/S

"■"	OPERATION MODE
NO LETTER	MOMENTARY
Z	LATCHING

SPECIFICATIONS:

- 1.SWITCH RATING: AC220V/0.5A.
- 2.MECHANICAL LIFE: $\geq 1,000,000$ cycles.
- 3.ELECTRICAL LIFE: $\geq 50,000$ cycles.
- 4.CONTACT RESISTANCE: $\leq 50m\Omega$.
- 5.INSULATION RESISTANCE: $\geq 100M\Omega(500VDC)$.
- 6.DIELECTRIC STRENGTH: 1,500V, RMS 50HZ, 1min.
- 7.OPERATING TEMPERATURE: $-25^{\circ}C \sim +55^{\circ}C$ (NO FREEZING).
- 8.OPERATING FORCE: ABOUT 2.5N.
- 9.OPERATING TRAVEL: ABOUT 3mm.
- 10.TORQUE: ABOUT 0.6Nm MAX.APPLIED TO NUT.
- 11.IP CLASS: IP40(IP65 CAN MADE TO ORDER), IK07.
- 12.TERMINAL TYPE: PIN TERMINAL(2.8 X 0.5mm).
- 13.GENERAL TOLERANCE: 0-18mm= ± 0.25 , 18-80mm= ± 0.52 .

MATERIALS:

- 1.CONTACT: SILVER ALLOY.
- 2.BUTTON: STAINLESS STEEL.
- 3.BODY: STAINLESS STEEL.
- 4.BASE: PA.

BRAND 品牌

ONPOW 欧宝龙®

红波按钮制造有限公司

ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.

TITLE 名称		ONPOW61 SERIES ANTI-VANDAL PUSH BUTTON				UNIT 单位	mm				
DWG NO. 图号		ONPOW6116F		SCALE 比例		1.4 : 1	SIZE 图纸	A4			
FILE NAME 档案名称		ONPOW6116 _DWG		DRAWN 制图		YDY 2022/06/25		SHEET 张	1/1	REV. 更改	1

1

2

3

4

5

6

7