


Hexalobular (6 Lobe) socket button head screws fully threaded

BN 6404



Standard	~ISO 7380-1,
Additional information	Fasteners to the given specification have a reduced loadability due to the head geometry according to ISO 898-1.
Headform	Button
Drive	Hexalobular socket
Thread	fully threaded
Material	Steel
Property class	08.8 / 8.8 (The head marking is determining)
Surface	zinc plated blue

Article no.	d1	L	d2 max.	k max.	Hexalobular socket	t max.	A~
3271436	M2	3	3,5	1,3	X6	0,8	1,75
3271438	M2	4	3,5	1,3	X6	0,8	1,75
3271439	M2	5	3,5	1,3	X6	0,8	1,75
3271440	M2	6	3,5	1,3	X6	0,8	1,75
3271441	M2	8	3,5	1,3	X6	0,8	1,75
1477188	M2	10	3,5	1,3	X6	0,8	1,75
3271442	M2	12	3,5	1,3	X6	0,8	1,75
3645745	M2	16	3,5	1,3	X6	0,8	1,75
3645746	M2,5	3	4,7	1,5	X8	0,92	2,4
3271443	M2,5	4	4,7	1,5	X8	0,92	2,4
3271444	M2,5	5	4,7	1,5	X8	0,92	2,4
3271445	M2,5	6	4,7	1,5	X8	0,92	2,4
3271446	M2,5	8	4,7	1,5	X8	0,92	2,4
3271447	M2,5	10	4,7	1,5	X8	0,92	2,4

Article no.	d1	L	d2 max.	k max.	Hexalobular socket	t max.	A~
3271448	M2,5	12	4,7	1,5	X8	0,92	2,4
3271449	M2,5	16	4,7	1,5	X8	0,92	2,4
3645747	M2,5	20	4,7	1,5	X8	0,92	2,4
3645748	M3	3	5,7	1,65	X10	1	2,8
3148111	M3	4	5,7	1,65	X10	1	2,8
3148113	M3	5	5,7	1,65	X10	1	2,8
1982990	M3	6	5,7	1,65	X10	1	2,8
1983385	M3	8	5,7	1,65	X10	1	2,8
1983393	M3	10	5,7	1,65	X10	1	2,8
1983407	M3	12	5,7	1,65	X10	1	2,8
5523987	M3	(14)	5,7	1,65	X10	1	2,8
1983415	M3	16	5,7	1,65	X10	1	2,8
3055580	M3	20	5,7	1,65	X10	1	2,8
3057192	M3	25	5,7	1,65	X10	1	2,8
3271450	M3	30	5,7	1,65	X10	1	2,8
3645749	M3	35	5,7	1,65	X10	1	2,8
3645750	M3	40	5,7	1,65	X10	1	2,8
3645751	M4	4	7,6	2,2	X20	1,4	3,95
3271451	M4	5	7,6	2,2	X20	1,4	3,95
1983547	M4	6	7,6	2,2	X20	1,4	3,95
1983555	M4	8	7,6	2,2	X20	1,4	3,95
1983563	M4	10	7,6	2,2	X20	1,4	3,95
1983571	M4	12	7,6	2,2	X20	1,4	3,95
3057194	M4	(14)	7,6	2,2	X20	1,4	3,95
1983636	M4	16	7,6	2,2	X20	1,4	3,95
1983644	M4	20	7,6	2,2	X20	1,4	3,95
1983652	M4	25	7,6	2,2	X20	1,4	3,95
3055581	M4	30	7,6	2,2	X20	1,4	3,95
3057195	M4	35	7,6	2,2	X20	1,4	3,95
3271452	M4	40	7,6	2,2	X20	1,4	3,95
3645752	M4	45	7,6	2,2	X20	1,4	3,95
3645753	M4	50	7,6	2,2	X20	1,4	3,95
3645754	M5	5	9,5	2,75	X25	1,6	4,5
1983660	M5	6	9,5	2,75	X25	1,6	4,5
1678183	M5	8	9,5	2,75	X25	1,6	4,5
1678205	M5	10	9,5	2,75	X25	1,6	4,5
1678221	M5	12	9,5	2,75	X25	1,6	4,5
3057196	M5	(14)	9,5	2,75	X25	1,6	4,5
1678256	M5	16	9,5	2,75	X25	1,6	4,5
1678477	M5	20	9,5	2,75	X25	1,6	4,5
1678493	M5	25	9,5	2,75	X25	1,6	4,5
1678515	M5	30	9,5	2,75	X25	1,6	4,5
3645755	M5	35	9,5	2,75	X25	1,6	4,5
3055582	M5	40	9,5	2,75	X25	1,6	4,5
3271453	M5	45	9,5	2,75	X25	1,6	4,5
3645756	M5	50	9,5	2,75	X25	1,6	4,5
3645757	M5	60	9,5	2,75	X25	1,6	4,5
3645758	M6	6	10,5	3,3	X30	1,9	5,6
1679023	M6	8	10,5	3,3	X30	1,9	5,6
1679058	M6	10	10,5	3,3	X30	1,9	5,6

Article no.	d1	L	d2 max.	k max.	Hexalobular socket	t max.	A~
1639366	M6	12	10,5	3,3	X30	1,9	5,6
3057197	M6	(14)	10,5	3,3	X30	1,9	5,6
1639382	M6	16	10,5	3,3	X30	1,9	5,6
1858475	M6	20	10,5	3,3	X30	1,9	5,6
1858483	M6	25	10,5	3,3	X30	1,9	5,6
1858491	M6	30	10,5	3,3	X30	1,9	5,6
3271454	M6	35	10,5	3,3	X30	1,9	5,6
3055583	M6	40	10,5	3,3	X30	1,9	5,6
3645759	M6	45	10,5	3,3	X30	1,9	5,6
3057198	M6	50	10,5	3,3	X30	1,9	5,6
3645760	M6	55	10,5	3,3	X30	1,9	5,6
3645761	M6	60	10,5	3,3	X30	1,9	5,6
1858505	M8	10	14	4,4	X40	2,6	6,75
1858513	M8	12	14	4,4	X40	2,6	6,75
1858564	M8	16	14	4,4	X40	2,6	6,75
1858572	M8	20	14	4,4	X40	2,6	6,75
1858580	M8	25	14	4,4	X40	2,6	6,75
1858602	M8	30	14	4,4	X40	2,6	6,75
3271455	M8	35	14	4,4	X40	2,6	6,75
1858637	M8	40	14	4,4	X40	2,6	6,75
3645762	M8	45	14	4,4	X40	2,6	6,75
3055584	M8	50	14	4,4	X40	2,6	6,75
3645763	M8	60	14	4,4	X40	2,6	6,75