





FOR 客户名称	APPROVED 客户确认签字	ATTN 销售负责人



PART NUMBER: ONPOW6125F-11■/S

"■"	OPERATION MODE
NO LETTER	MOMENTARY
Z	LATCHING

SPECIFICATIONS:

1.SWITCH RATING: AC220V/0.5A.

2.MECHANICAL LIFE: ≥1,000,000 cycles.

3.ELECTRICAL LIFE: ≥50,000 cycles.

4.CONTACT RESISTANCE: ≤50mΩ.

5.INSULATION RESISTANCE: ≥100MΩ(500VDC).

6.DIELECTRIC STRENGTH: 1,500V, RMS 50HZ, 1min.

7.OPERATING TEMPERATURE: -25°C~ +55°C(NO FREEZING).

8.OPERATING FORCE: ABOUT 2.5N.

9.OPERATING TRAVEL: ABOUT 3mm.

10.TORQUE: ABOUT 0.6Nm MAX.APPLIED TO NUT.

11.IP CLASS: IP40(IP65 CAN MADE TO ORDER), IK07.

12.TERMINAL TYPE: PIN TERMINAL(2.8 X 0.5mm).

13.GENERAL TOLERANCE:0-18mm=±0.25, 18-80mm=±0.52.

MATERIALS:

1.CONTACT: SILVER ALLOY.

2.BUTTON: STAINLESS STEEL.

3.BODY: STAINLESS STEEL.

4.BASE: PA.

BRAND 品牌		红波按钮制造有限公司			
ONPOW 欧宝龙®		ONPOW PUSH BUTTON MANUFACTURE CO.,LTD.			
TITLE 名称	ONPOW61 SERIES ANTI-VANDAL PUSH BUTTON			UNIT 单位	mm
DWG NO. 图号	ONPOW6125F			SCALE 比例	1.2 : 1
FILE NAME 档案名称	ONPOW6125 .DWG	DRAWN 制图	YDY 2022/06/25	SHEET 张	1/1
			REV. 更改	1	