



Product: [9116](#)

Broadband Coax, Series 6, 18 AWG Solid BCCS, Foil + 60% AL Braid, PVC Jkt, CM

Product Description

Broadband Coax, Series 6, 18 AWG Solid Bare Copper Covered Steel Conductor, PE Insulation, Foil + 60% Aluminum Braid Shield, PVC Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	Broadband, Cable Television (CATV), RF drop cable, Over-The-Air (OTA) antennas
------------------------	--

Construction Details

Series Type:	6
--------------	---

Conductor

Size	Stranding	Nom. Diameter	Material
18 AWG	Solid	0.040 in	BCCS - Bare Copper Covered Steel

Insulation

Material	Nom. Insulation Diameter
PE - Polyethylene (Foam)	0.180 in (4.57 mm)

Outer Shield

Layer	Outer Shield Type	Material	Material Trade Name	Coverage
1	Tape	Tri-Laminate (Alum+Poly+Alum)	Duobond® II	100%
2	Braid	Aluminum		60%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.270 in (6.86 mm)

Overall Cable Diameter (Nominal):	0.270 in (6.86 mm)
-----------------------------------	--------------------

Electrical Characteristics

Return Loss (RL)

Frequency	Min. Structural Return Loss
5 - 1000 MHz	20 dB

Attenuation

Frequency	Max. Attenuation
5 MHz	0.58 dB/100ft
55 MHz	1.60 dB/100ft
211 MHz	3.05 dB/100ft
250 MHz	3.30 dB/100ft
270 MHz	3.37 dB/100ft
300 MHz	3.55 dB/100ft
330 MHz	3.74 dB/100ft
350 MHz	3.85 dB/100ft
400 MHz	4.15 dB/100ft

450 MHz	4.40 dB/100ft
500 MHz	4.66 dB/100ft
550 MHz	4.90 dB/100ft
600 MHz	5.10 dB/100ft
750 MHz	5.65 dB/100ft
870 MHz	6.11 dB/100ft
1000 MHz	6.55 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
28 Ohm/1000ft (92 Ohm/km)	9 Ohm/1000ft (30 Ohm/km)	16.2 pF/ft (53.1 pF/m)	75 Ohm	83%

Voltage

UL Voltage Rating
300 V (CM)

Mechanical Characteristics

Temperature

Operating
-40°C to +75°C

Bend Radius

Installation Min.
2.7 in

Max. Pull Tension:	150 lbs (68 kg)
Bulk Cable Weight:	27 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 UL Loading
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	CM, CATV
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	ANSI/SCTE 74
Plenum Number:	9116P

History

Update and Revision:	Revision Number: 0.367 Revision Date: 01-04-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC/EAN
9116 290U1000	Beige, Light	UnReel	1,000 ft	612825224389
9116-0101000	Black	Reel	305 m	8719605020123
9116-K101000	Black	Reel	305 m	8719605020154
9116 010500	Black	Reel	500 ft	612825224426
9116 010U500	Black	UnReel	500 ft	612825224457
9116 010S700	Black	Reel	700 ft	612825348313
9116 0101000	Black	Reel	1,000 ft	612825224440
9116 010U1000	Black	UnReel	1,000 ft	612825348320
9116 010N1000	Black	Reel w/Small Barrel	1,000 ft	612825224433
9116 009500	White	Reel	500 ft	612825224396
9116 0091000	White	Reel	1,000 ft	612825224419
9116 009U1000	White	UnReel	1,000 ft	612825348337
9116 009N1000	White	Reel w/Small Barrel	1,000 ft	612825224402

9116 Q5H1000	White, Neutral	Reel	1,000 ft	612825224372
9116 Q5HU1000	White, Neutral	UnReel	1,000 ft	612825224488

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.