

Ratchet Pipe Threader Set

7CA0606S

- Use to thread pipe for attach fitting and connector
- Thread sizes:
4pcs interchangeable dies 1/2", 3/4", 1" and 1-1/4"
- Ratchet threader assembly with extension handle



7CA0606S1



7
PC.

KT NO. Thread Plug Gauge Capacity Contents

7.1 1/2


7CA0606S	BSPT	1/2"	7CA61-A01	7CA61-A011			
		3/4"	7CA61-A02	7CA61-A021			
		1"	7CA61-A03	7CA61-A031			
		1-1/4"	7CA61-A04	7CA61-A041			
7CA0606S1	NPT	1/2"	7CA61-B01	7CA61-B011			 7CA61P03
		3/4"	7CA61-B02	7CA61-B021			
		1"	7CA61-B03	7CA61-B031			
		1-1/4"	7CA61-B04	7CA61-B041			

180° Tube Bender

7CA11M

7CA11S

- Suitable for use in refrigeration and air-conditioning, oil supply, heating installations, floor heating
- Able to accurately bend soft copper pipes, brass pipes, aluminum pipes, and thin-walled iron pipes (walls less than 0.6 mm) up to 180°
- Bending with the bending radius display and measurement scale



7CA11-10M / 7CA11-12S
7CA11-16S



7CA11-15M / 7CA11-16M
7CA11-20S / 7CA11-24S

KT NO.	mm	max. (mm)	R(radius) inch	mm	Overall length inch	mm	964	1 / 20
7CA11-10M	10	0.9	15/16	24	13	334	964	1 / 20
7CA11-15M	15	1.2	2-1/4	57	30	758	2832	1 / 8
7CA11-16M	16	1.2	2-1/4	57	30	758	2832	1 / 8

KT NO.	inch	max. (inch)	R(radius) inch	mm	Overall length inch	mm	964	1 / 20
7CA11-12S	3/8	0.035	15/16	24	13	334	964	1 / 20
7CA11-16S	1/2	0.049	1-1/2	38	20	493	1833	1 / 12
7CA11-20S	5/8	0.049	2-1/4	57	30	758	2832	1 / 6
7CA11-24S	3/4	0.049	3	76	30	758	3330	1 / 6