

Technical data sheet

Twin gland, PG thread, light grey

Item no. 2024160



With removable polystyrene lid, as well as two connection thread sealing rings made of polyethylene.



UF Duroplast, Aminoplast, type 131.5

Additional product text 1	113/16: with connection thread Pg 16, 2 half glands Pg 13.5 for cable diameter 6.5–10.5 mm.
---------------------------	---

Master data

Item no.	2024160
Type	113 PG16 LGR
Description 1	Twin cable threaded connection
Dimension	PG16
Colour	Light grey
RAL number	7035
Material	Duroplast, Aminoplast, type 131.5
Material symbol	UF
Smallest sales unit (VG)	5,00 Piece
Weight	4,36 kg/100 pc.


Technical data sheet

Twin gland, PG thread, light grey

Item no. 2024160



Technical data



Version	Straight
Bend protection	☐
Sealing range D	6,50 - 10,50 mm
explosion-proof	☐
Flat cable threaded connection	☐
For Ex zone	Without
Flame resistant	Flame resistant to VDE 0471/DIN 695 Part 2-1, test temperature 650 °C
Thread	Pg 16
Thread type	PG
Fibre-glass reinforced	☐
Halogen-free	☒
Multiple sealing insert	☐
With locknut	☐
Impact-resistant	☐
Protection rating	IP54
Splittable gland	☐
Strain relief option	☐