

PRODUCT-DETAILS

TY24MFR-RW

TY24MFR FOR RAILWAY



General Information

Extended Product Type	TY24MFR-RW
Product ID	7TCG009570R0009
EAN	5415022180367
Catalog Description	TY24MFR FOR RAILWAY
Long Description	Ty-Rap Cable Tie Flame retardant Length of 140mm (5.5 Inches), Width of 3.6mm (0.14 Inch), Thickness of 1.3mm (0.05 Inch), Maximum Bundle Diameter 35mm (1.38 Inches), Tensile Strength Rating of 134 Newtons (30 Pounds) White Polyamide 6.6 for Railway

Ordering

EAN	5415022180367
UPC	786209719140
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.14 in 3.6 mm
Product Net Depth / Length	5.5 in 140 mm

Container Information

Package Level 1 Units	1000 piece
Package Level 1 Width	11.39 in 289 mm
Package Level 1 Height	1.57 in 40 mm
Package Level 1 Depth / Length	11.79 in 299 mm
Package Level 2 Units	10000 piece
Package Level 2 Width	11 in 279 mm
Package Level 2 Height	9.03 in 229 mm
Package Level 2 Depth / Length	14.14 in 359 mm

Technical UL/CSA

Flammability According to UL94	V-0
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Bundle Diameter	0.08 to 1.38 in 2 to 35 mm
Color	White
Effective Date	20130731
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	OTHER ARTICLES OF PLASTIC
Product Type	Railway
Standards	UL E49405
Tensile Strength	30 lb 134 N
Thickness	0.05 in 1.3 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000478
Instructions and Manuals	TY24MFR-RW
REACH Declaration	9AKK107992A4002
RoHS Information	9AKK107991A8072

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

