



PRODUCT-DETAILS

TY5272MR

CABLE TIE 120LB 9IN NATURAL NYLON



General Information

Extended Product Type	TY5272MR
Product ID	7TCG009460R0102
EAN	5414363065760
Catalog Description	CABLE TIE 120LB 9IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21S Rated for AH-2 Plenum and as a Flexible Cable and Conduit Support, Length of 224mm (8.8 Inches), Width of 6.9mm (0.27 Inch), Thickness of 1.5mm (0.06 Inches), Tensile Strength Rating of 534 Newtons (120 Pounds), Euroslot Packaging

Ordering

EAN	5414363065760
UPC	786210613789
Country of Origin	Hungary (HU)
Customs Tariff Number	3926909990
Selling Unit of Measure	each

Dimensions

Product Net Width	0.275 in 6.99 mm
Product Net Depth / Length	8.75 in 222.3 mm

Container Information

Package Level 1 Units	50 piece
Package Level 2 Units	5000 piece
Package Level 2 Width	15.4 in 391 mm
Package Level 2 Height	11 in 279 mm
Package Level 2 Depth / Length	23.6 in 599 mm

Technical UL/CSA

Flammability According to UL94	V-2
--------------------------------	-----

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19980621
Lock Type	Stainless Steel Barb
Material	Nylon/Polyamide 6.6
Product Name	TY-RAP FASTENING
Product Type	High Performance
RoHS Date	9AKK107991A8366
Tensile Strength	120 lb 540 N
Thickness	0.07 in 1.78 mm

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TDS000487
Declaration of Conformity - CE	9AKK107492A9841
Instructions and Manuals	TY5272MR
REACH Declaration	9AKK107992A8781
RoHS Information	9AKK107991A8366

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
ETIM 8	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

