

FK-441

Technische Daten | Technical Data

Empf. Mindesttrasterabstand rec. centre spacing:	2,30 mm	.090 inches
Federkraft Spring Force:	0,8 N	2.88 oz.
Maximaler Federweg Max. Travel:	2,25 mm	.089 inches
Empfohlener Kontakthub Recomm. (rated) Travel:	1,52 mm	.060 inches
Temperaturbereich Temperature range:	-55°C bis +250°C	-67°F to +482°F
Typischer Widerstand Typical Resistance:	100 mΩ	100 mΩ
Typischer Nennstrom Rated Current Load:	3 A	3 amps
E-Maß Extension Height:	8,22 mm	.323 inches
Bauform, Anschluss Design, Connection Type:	THT-t	

Werkstoffe | Materials

Kolben Plunger:	Cu-Legierung, vergoldet Copper alloy, gold plated
Gehäusehülse Barrel:	Neusilber Nickel silver
Feder Spring:	Edelstahl Stainless steel

