

# Combination pliers

406/1BI



## Profiles

---




## Standards

---

ISO 5746

## Product features

- material: premium plus carbon steel
- drop forged, entirely hardened and tempered
- cutting edges induction hardened
- head polished
- surface finish: chrome plated to standard ISO 1456:2009
- heavy duty double - component handles
- jet stamp UNIOR
- made according to standard ISO 5746






|  | L   | B  | C  | A    |  |
|----------------------------------------------------------------------------------|-----|----|----|------|-------------------------------------------------------------------------------------|
| 607870                                                                           | 160 | 24 | 35 | 9.5  | 224                                                                                 |
| 607871                                                                           | 180 | 27 | 38 | 10   | 274                                                                                 |
| 607872                                                                           | 200 | 29 | 41 | 10.5 | 341                                                                                 |
| 608354                                                                           | 220 | 32 | 47 | 11   | 421                                                                                 |

cutting capacity (10N=1kg)

|  | L   | max 1600 N/mm <sup>2</sup> Ø↑ | max 650 N/mm <sup>2</sup> Ø↑ |
|----------------------------------------------------------------------------------|-----|-------------------------------|------------------------------|
| 607870                                                                           | 160 | 1,6                           | 2,0                          |
| 607871                                                                           | 180 | 1,8                           | 2,5                          |
| 607872                                                                           | 200 | 2,0                           | 2,5                          |
| 608354                                                                           | 220 | 2,0                           | 3,0                          |

\* Images of products are symbolic. All dimensions are in mm, and weight in grams. All listed dimensions may vary in tolerance.

## Usage (pictures)



## Safety tips



- Pliers should be oiled regularly. A drop of oil at the hinge will lengthen the tool life and assure easy operation.



- Don't use pliers for cutting hardened wire, unless specifically manufactured for this purpose.
- Don't expose pliers to excessive heat. This may ruin the tool.

- When cutting wire with pliers, you should always wear glasses or goggles.
- Handles are provided for comfort. They are not intended to give user any degree of protection against electric shocks and should never be used on live electric circuits.
- Don't use pliers as a hammer.
- Don't hammer on the handles. They may crack or break.
- Don't extend the length of plier handles to secure greater leverage.
- Don't use pliers on nuts or bolts. A wrench will do a better job and with less risk of damage to the fastener.

## Frequently asked questions

**The head profile on the screw has deformed to such an extent that it cannot be unscrewed with a screwdriver. Which Unior tool can be used in this case?**

407/4DP screw pliers are the best choice for unscrewing screws with a damaged head profile.