



CSB P M 203 x 5/8 x 1.8 x 42 - 1pc

CIRCULAR SAW BLADES FOR METAL

- 1. Engineered tooth geometry for optimum performance.
- 2. Top grade carbide and cermet tooth tips for superior lifetime.
- 3. Fully hardened and tensioned blade body for accurate cuts.
- 4. Deep gullets provide rapid and efficient chip removal.
- 5. Laser cut resin filled expansion slots for noise and vibration dampening.
- Cuts clean. Burr free edges reduce extra finishing processes.
- Cuts cool. The cut material can be handled immediately after cutting.
- Cuts fast. Quicker than all other conventional cutting methods.
- Cost cutter. Less expensive per cut than abrasive discs.
- Reduced noise.
- Reduced vibration.
- Total safety: no sparks, no coolants, cool to touch.
- Blade 4932478815 is supplied in natural silver finish



Aluminium	✗
Angle iron	✓
Article Number	48404515
Blade diameter (inch)	8
Blade diameter (mm)	203
Bore size (inch)	5/8
Bore size (mm)	5/8 "
Contents	42 tooth blade for cutting steel > 2.5 mm, steel panels, pipe, angle iron and steel channel.
Cutting width (kerf) (mm)	1.8
Material wall thickness (mm)	>2.5
Mild steel	✓