



Product: [74002PU](#)

DataTuff® 5E, 4PR #26 Str BC, PO ins, SF/UTP, PUR HF jkt, AWM 20549

Product Description

DataTuff® 5E, 4 Pair AWG 26 Bare Copper - Stranded, Polyethylene insulation, SF/UTP - Overall Braid + Foil shielding, PUR Halogen Free jacket , AWM 20549

Technical Specifications

Product Overview

Suitable Applications:	harsh environment, IIoT, factory or process automation, video, audio, data communication, etc.
------------------------	--

Construction Details

Conductor

Size	Stranding	Material	No. of Pairs	No. of Elements
26 AWG	7x0.16 mm	BC - Bare Copper	4	8

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	0.98 mm (0.039 in)	White/Blue & Blue, White/Orange & Orange, White/Green & Green, White/Brown & Brown

Cable Core

Description
4 pairs twisted to cable core covered with a polyester foil

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	
Braid	Tinned Copper (TC)	80%

Table Notes:	Aluminum outside
--------------	------------------

Outer Jacket

Material	Nom. Diameter
PUR - Polyurethane (Halogen Free)	6.5 mm (0.26 in)

Table Notes:	Flame Retardant Sheath
Overall Cable Diameter (Nominal):	6.5 mm (0.26 in)

Electrical Characteristics

Electricals

Max. Conductor DCR	Max. Mutual Capacitance	Max. Capacitance Unbalance	Nom. Characteristic Impedance
145 Ohm/km	56 pF/m (17 pF/ft)	160 pF/100m	100 Ohm

Delay

Max. Delay Skew	Nom. Velocity of Prop.
40 ns/100m	60%

High Frequency

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]
-----------------	-----------------------------------	----------------	------------------	-------------------------	-----------------------------	----------------------------

0.772		67	64			19.4
1	3.2 dB/100m	65.3	62.3	63.8	60.8	20
4	6 dB/100m	56.3	53.3	51.8	48.8	23
10	9.5 dB/100m	50.3	47.3	43.8	40.8	25
16	12.1 dB/100m	47.2	44.2	39.7	36.7	25
20	13.6 dB/100m	45.8	42.8	37.8	34.8	25
25	15.3 dB/100m	44.3	41.3	35.8	32.8	24.3
31.25	17.1 dB/100m	42.9	39.9	33.9	40.9	23.6
62.5	24.8 dB/100m	38.3	35.4	27.9	24.9	21.5
100	32 dB/100m	35.3	32.3	23.8	20.8	20.1

Voltage

Voltage Rating
450 V DC and 300 V AC

Mechanical Characteristics

Temperature

Operating	Installation	Storage
-40°C to +80°C	-15°C To +60°C	-40°C to +80°C

Bend Radius

Stationary Min.	Installation Min.
35 mm (1.4 in)	70 mm

Max. Pull Tension:	80 N (18 lbf)
--------------------	---------------

Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Sunlight Resistance, Oil Resistance
AWM Compliance:	AWM 20549
Data Category:	Category 5e
TIA/EIA Compliance:	ANSI/TIA 568.2-D
ISO/IEC Compliance:	ISO/IEC 11801-1
CENELEC Compliance:	EN 50173-1
European Halogen Free Standards:	IEC 60754-1 - Halogen Amount = Zero, IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity = 10 µS/mm, IEC 60754-2 - Halogen Acid Gas Amount - Min. pH = 4.3
European Directive Compliance:	EU CE Mark

History

Update and Revision:	Revision Number: 0.255 Revision Date: 03-04-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	EAN
74002PU.01305	Black	Reel	305 m	8719605013095
74002PU.01500	Black	Reel	500 m	8719605013101
74002PU.011000	Black	Reel	1,000 m	8719605013088

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.