




Remark : IP67



ELECTRICAL SPECIFICATIONS

Diameter	42.5 $\pm$ 0.3 mm
Height	22.4 $\pm$ 0.5 mm
Back Dia.	23 $\pm$ 0.3 mm
Output S.P.L.	85 $\pm$ 3 dB [At 3.0W/1.0m, ave. at 0.3K, 0.6K, 1.0K, 2.0K Hz]
Impedance	4 ohm $\pm$ 15% [At 2KHz / 1V]
Resonant Freq. [Fo]	180 Hz $\pm$ 20 % [At 1V]
Freq. Response	Fo ~ 20K Hz
Rated Input Power	3W
Max. Input Power	5W
Buzzer & Rattles	Must Be Normal [Sine Wave 3.46V, F0 ~ 5K Hz]
Load Test	Must Be Normal [White Noise 3W, 24 Hours]
Heat Test	Must Be Normal [85 $\pm$ 3 $^{\circ}$ C, 24 Hours]
Cold Test	Must Be Normal [-40 $\pm$ 3 $^{\circ}$ C, 24 Hours]
Humidity Test	40 $\pm$ 3 $^{\circ}$ C, 92 ~ 95% R.H. 24 Hours
Case Material	Metal
Magnet	Internal Magnet - NdFeB
Operating Temperature	-40 ~ +85 $^{\circ}$ C
Storage Temperature	-40 ~ +85 $^{\circ}$ C
Weight	36 $\pm$ 8% g