

**SAIB-3-IDC-M8 SMALL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Individual cable lengths are often required nowadays. In order to meet these demands, Weidmüller offers a wide range of plug-in connectors for custom assembly.

Male plugs and female sockets for customisable assembly for M8, M12, M16 and 7/8" connections which are highly robust and ideally suited to machine engineering, for instance. The M8 round plug-in connectors are particularly suited to applications where space is limited.

The IDC is simple and quick to assemble since this technology allows the conductor to be inserted directly into the terminal point, without crimping or having to strip the insulation. It also has excellent functional security.

**General ordering data**

|            |                                                         |
|------------|---------------------------------------------------------|
| Version    | Field attachable connector, M8, Female socket, straight |
| Order No.  | <a href="#">1784030001</a>                              |
| Type       | SAIB-3-IDC-M8 SMALL                                     |
| GTIN (EAN) | 4032248429981                                           |
| Qty.       | 1 pc(s).                                                |

## SAIB-3-IDC-M8 SMALL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |
|------------|--------|
| Net weight | 14.6 g |
|------------|--------|

## Temperatures

|                             |        |                             |       |
|-----------------------------|--------|-----------------------------|-------|
| Operating temperature, min. | -25 °C | Operating temperature, max. | 85 °C |
|-----------------------------|--------|-----------------------------|-------|

## Technical data customisable plug-in connectors

|                                |                      |                                |                                    |
|--------------------------------|----------------------|--------------------------------|------------------------------------|
| Cable diameter                 | 3.2...5.4 mm         | Cable diameter, max.           | 5.4 mm                             |
| Cable diameter, min.           | 3.2 mm               | Coding                         | none, A                            |
| Conductor cross-section, max.  | 0.34 mm <sup>2</sup> | Conductor cross-section, min.  | 0.14 mm <sup>2</sup>               |
| Connection cross-section, max. | 0.34 mm <sup>2</sup> | Connection cross-section, min. | 0.14 mm <sup>2</sup>               |
| Contact surface                | tinned               | Housing main material          | CuZn                               |
| Insulation strength            | 10 <sup>8</sup> Ω    | Number of poles                | 3                                  |
| Plugging cycles                | ≥ 50                 | Pollution severity             | 3                                  |
| Protection degree              | IP67                 | Rated current                  | 4 A                                |
| Rated voltage                  | 32 V                 | Rated voltage                  | 32 V                               |
| Shield connection              | No                   | Temperature range of housing   | -25...+85 °C                       |
| Threaded ring material         | Diecast zinc         | Type of connection             | Insulation displacement connection |

## Standards

|                    |                 |
|--------------------|-----------------|
| Connector standard | IEC 61076-2-104 |
|--------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002635    | ETIM 7.0    | EC002635    |
| ETIM 8.0    | EC002635    | ECLASS 9.0  | 27-44-01-02 |
| ECLASS 9.1  | 27-44-01-03 | ECLASS 10.0 | 27-44-01-02 |
| ECLASS 11.0 | 27-44-01-02 | ECLASS 12.0 | 27-44-01-16 |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Downloads

|                  |                                                                        |
|------------------|------------------------------------------------------------------------|
| Engineering Data | <a href="#">CAD data – STEP</a>                                        |
| Catalogues       | <a href="#">Catalogues in PDF-format</a>                               |
| Brochures        | <a href="#">FL FIELDWIRING EN</a><br><a href="#">FL FIELDWIRING EN</a> |