

Needle File Set

- Pouch material : PVC

1036ZQ

- Perfect for filing off sharp edges, reshaping cuts or reaming drilled holes
- #60 grit diamond coating surface



6
PC.

Contents

L
mm



75135-06	75435-06			
75235-06	75535-06	160	95	10 / 120
75335-06	75035-06			

Tapered Reamer

7E61001



- For deburring and sizing the diameter of holes 1/8" to 3/8"
- Suitable for metal, wood or plastic



70



24 / 96



Tap Wrench

39110312M



KT NO.

Size
Inch

L
mm



39110312M	1/8-1/2	M3-M12	196	128	1 / 100
-----------	---------	--------	-----	-----	---------

Threaded Coil-Insert Repair Set

11311MQ

- Thread tap for most common metric size : M5, M6, M8 and M10
- Used for repairing and restoring damaged threads
- Suitable for machine, engine and other automotive repair applications



119
PC.

Metal case size (mm) : 350 x 216 x 40

Contents



2.78



1 / 5

	Screw-Coil:	
	M5x0.8x1.5D(L:7.5mm)	25 PC.
	M6x1.0x1.5D(L:9mm)	25 PC.
	M8x1.25x1.5D(L:12mm)	25 PC.
	M10x1.5x1.5D(L:15mm)	25 PC.
	Tap:	
	M5x0.8	1 PC.
	M6x1.0	1 PC.
	M8x1.25	1 PC.
	M10x1.5	1 PC.
	Tang Punch:	
	M5x0.8	1 PC.
	M6x1.0	1 PC.
	M8x1.25	1 PC.
	M10x1.5	1 PC.
	Drill:	
	5.2mm	1 PC.
	6.3mm	1 PC.
	8.3mm	1 PC.
	10.4mm	1 PC.
	Main Tool:	
	M5x0.8	1 PC.
	M6x1.0	1 PC.
	M8x1.25	1 PC.
	M10x1.5	1 PC.
3571-08		3/8" drive sliding T-handle
3764-55G		3/8" drive mini reversible ratchet
39123012M		3/8" tap holder

