

Accessory

2293

1/4"

- Multi-function extension bar and offset extension bar
- Hex key is applicable to the hex shank
- Max. torque : 35 N·m
- DIN 3123



KT NO.	Overall length			
	inch	mm		
2293-02	2	55	24	30 / 480
2293-03	3	75	34	20 / 400
2293-04	4	100	44	15 / 240
2293-06	6	150	65	15 / 300

KT No. & D1

2311

1/4"

- Flexible extension bar



KT NO.	Overall length			
	inch	mm		
2311-06	6	150	65	12 / 240
2311-12	12	300	89	12 / 120
2311-18	18	450	112	20 / 200

KT No. & D1

2312

1/4"

- Flexible extension bar



KT NO.	Overall length			
	inch	mm		
2312-06	6	150	59	12 / 240

2792

1/4"

- Universal joint
- DIN 3123



KT NO.	Overall length			
	inch	mm		
2792	1 - 1/2	36	22	24 / 384

2813

1/4"

- Adapter
- Convert to 3/8" drive
- DIN 3123



KT NO.	Spec.		
2813	1/4" F x 3/8" M	20	12 / 360

3/8" drive (M) ← 1/4" drive (F)

213312DF

1/4"

- Magnetic screwdriver handle
- DIN 3126



KT NO.	Overall length			
	inch	mm		
213312DF	12	300	132	2 / 40

2177DF

1/4"

- Spinner handle
- DIN 3122



KT NO.	Overall length			
	inch	mm		
2177DF	12-1/4	310	126	6 / 60

2178DF

2179DF

1/4"

- Spinner handle
- DIN 3122



2178DF (PP + TPR)



2179DF (PP)

KT NO.	Overall length			
	inch	mm		
2178DF	6	150	76	6 / 120
2179DF	6	150	90	12 / 192

2178TG

1/4"

- Spinner handle
- DIN 3122



KT NO.		mm	mm		
2178TG	1/4	115	154	94	6 / 96

2452

1/4"

- Flexible handle
- Action degree -180°
- DIN 3122




2452DK

KT NO.	Overall length			
	inch	mm		
2452-05F	5	130	86	15 / 270
2452DK	renewal kits			